



Dimmer Compatibility guide



Candle



PAR



Type A



**Misc.
G25, ST19**



BR

PHILIPS



16w(100w)
A21



12w(75w)
A21



9.5w(60w)
A19



9.5w(60w)
A19 WG



5.5w(40w)
A19



5.5w(40w)
A15 Clear WG

Applicable Philips Part Numbers			9290018368 (479881), 9290018369 (479899), 9290018370 (479493)			9290018873 (479873), 9290018668 (532993), 9290018367 (479477)			9290018363 (479857), 9290018364 (479865), 9290018365 (479451)			9290018373 (479444)			9290018371 (479428), 9290018361 (479840), 9290018669 (532985), 9290018362 (479436)			929001215004 (462529)		
Dimmer Company	Brand	Model No.	# of bulbs			# of bulbs			# of bulbs			# of bulbs			# of bulbs			# of bulbs		
			Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Cooper	REACT	RI061-VW-K2																		
Leviton	Decora	6161																		
Leviton	SureSlide	6613	1-9					1-13			1-15						1-25			
Leviton	SureSlide	6615P	1-5					1-6				X	1-8			1-14			1-13	
Leviton	SureSlide	6631																		
Leviton	SureSlide	6633	1-9					1-13			1-15				1-15				1-25	
Leviton	SureSlide	6672	1-9					1-13			1-15				1-15				1-25	
Leviton	SureSlide	6674																		
Leviton	Trimatron	6602	1-9					1-13			1-15				1-15				1-25	
Leviton	Trimatron	6681	1-9			1		2-13			1-15				1-15				1-25	
Leviton	Trimatron	6683																		
Leviton	Trimatron	6684																		
Leviton	IllumaTech	IPE04-1LZ																		
Leviton	IllumaTech	IPI06	1-9					1-13				X	1-15			1-15			1-25	
Leviton	IllumaTech	IPM10						-15											2-25	
Leviton	Monet	MNI06-1																		
Philips	Sunrise	SR1000VA120	1-9								1-15					2-15	1		2-25	
Philips	Sunrise	SR150LED120	1-9					1-13			1-15					1-15		X	2-25	1-3
Lightolier	Vega	V600VAU																		
Lightolier	Vega	V1000VAU																		
Lightolier	Sunrise	ZP600VA ²																		
Lightolier	Sunrise	ZP600																		
Lightolier	Vega	V600																		
Lightolier	Onset	OS600																		
Lightolier	Onset	OS600VA																		
Lightolier	Onset	OS1000VA																		
Lightolier	Astral Slider	A600																		
Lightolier	Astral Slider	AP600																		
Lightolier	MultiSet	MHP600VA																		
Lightolier	Momentum	MP2000VAI																		
WattStopper	Micro Decorator	DCD267-W	1-9					1013			1-15				1-15			10-15	X	1-25
WattStopper	Paddle	PDMLV-703-W																		
WattStopper	Slide	SDMLV-603-W																		
WattStopper	Slide	SD-603-W																		
Lutron	Skylark	CTCL-153P																		
Lutron	Diva	DVCL-153PD	1-9					1-13							1-15			1-15		1-3
Lutron	Diva	DVCL-153P v2 ²	1-9					1-13			1-15				1-15			1-15		1-3
Lutron	Diva	DVPDC-203																		
Lutron	Diva	DV-600P	1-9					1-13			1-15				1-15			1-15		1-25
Lutron	Diva	DV-603PG																		
Lutron	DIVA	DVELV-300P	1-9				1-6				1-15				1-8			1-15		1-13
Lutron	Glyder	GL-600P																		
Lutron	Maestro	MACL-153M v2 ²	1-9					1-13			1-15				1-15			1-15		1-25
Lutron	Maestro	MAELV-600																		
Lutron	Maestro	MALV-600																		
Lutron	Maestro	MRF2-6ND-120	1-9					1-13			1-15				1-15			1-15		1-25
Lutron	Nova	NLV600 ²																		
Lutron	Nova	NLV1000 ²	1-10					1-15			1-16				1-15			2-15	1	1-25
Lutron	Nova	NT-600-W																		
Lutron	Nova	NTELV-300																		
Lutron	Grafik Eye	QSGR-3P ²						1-15			1-15				1-15			1-15		1-25
Lutron	Qoto	Q-600P																		
Lutron	RADIO RA	RRD-6NA ²	1-9					1-13			1-15				1-15			1-15		1-3
Lutron	Skylark	S-600P																		
Lutron	Skylark	SELV-300P																		
Lutron	Skylark	SLV-600P	1-7					1-9			1-8				1-15			1-5	8-15	1-19
Lutron	Skylark	SCL153P v2 ²																		
Lutron	Toggle	TG-600P																		
Lutron	Credenza	TT-300																		
Lutron	Power Module	PHPM-WBX																		
Lutron	Verti	VTELV-600M-I																		
Lutron	Caseta	PD-6WCL (SD11)	1-9					1-13			1-15				1-15			1-15		1-3
Sensors																				
Lutron	Maestro	MSCL-OP153MH	1-9					1-13	1-13		1-15				1-15			1-15		1-25
Lutron	Maestro	MS-OPS2H	1-9					1-13			1-15				1-15			1-15		1-25
Leviton	Decora	IPS02	1-9					1-13			1-15				1-15			1-15		1-25
Leviton	Decora	IPS15	1-9					1-13			1-15				1-15			1-15		1-25
Panel Modules																				
Lutron	Panel Module	GP (Harrier) Card	1-15					1-15			1-15				1-15			1-15		1-25
Lutron	Panel Module	HW/LP-RPM-4U-120	1-15					1-15			1-15				1-15			1-15		1-25

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

WG	Warm Glow
AF	Air Flux
DS	Diamond Spark
CC	Clear Classic
DC	Die Cast
DW	Direct White
SO	Single Optic

PHILIPS



**5.5W(40W)
A15 Clear WG**



**7W(40W)
A15 CC WG**



**4.5W(60W)
A19**



**4.5W
A19 Filament**



**6W(40W)
A19**

Applicable Philips Part Numbers			929001215004 (462529)			9290011818 (458760, 458786, 458778)			929001210103 (461632), 929001210135 (465542), 929001273935 (466227), 929001274135 (466243)			9290012101 (461665)			9290011348 (455808), 9290011348 (455782), 9290011178 (453209), 9290011178 (453274), 9290011178 (454058), 9290011348 (455790)		
Dimmer Company	Brand	Model No.	# of bulbs			# of bulbs			# of bulbs			# of bulbs			# of bulbs		
			Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Cooper	REACT	RI061-VW-K2															
Leviton	Decora	6161															
Leviton	SureSlide	6613	1-25				1-21			1-33			1-33			1-12*	
Leviton	SureSlide	6615P		1-13			1-11			1-17			1-17			1-12*	
Leviton	SureSlide	6631															
Leviton	SureSlide	6633	1-25				1-21			1-33			1-33			1-12*	
Leviton	SureSlide	6672	1-25				1-21			1-33			1-33			1-12*	
Leviton	SureSlide	6674					1-21			1-10			1-10	11-33		1-12*	
Leviton	Trimatron	6602	1-25				1-21			1-33			1-33			1-12*	
Leviton	Trimatron	6681	1-25					1-21		1-33			1-33			1-12*	
Leviton	Trimatron	6683															
Leviton	Trimatron	6684															
Leviton	IllumaTech	IPE04-1LZ															
Leviton	IllumaTech	IPI06	1-25				1-21			1-33			1-33			1-12*	
Leviton	IllumaTech	IPM10		2-25			2-21			2-33			2-33	1		1-12*	1-12*
Leviton	Monet	MNI06-1															
Philips	Sunrise	SR1000VA120		2-25			2-21			2-33			2-33	1		1-12*	
Philips	Sunrise	SR150LED120		1-3			1-21			1-10			1-10	11-33		1-12*	
Lightolier	Vega	V600VAU															
Lightolier	Vega	V1000VAU															
Lightolier	Sunrise	ZP600VA ²															
Lightolier	Sunrise	ZP600															
Lightolier	Vega	V600															
Lightolier	Onset	OS600															
Lightolier	Onset	OS600VA															
Lightolier	Onset	OS1000VA															
Lightolier	Astral Slider	A600															
Lightolier	Astral Slider	AP600															
Lightolier	MultiSet	MHP600VA															
Lightolier	Momentum	MP2000VAI															
WattStopper	Micro Decorator	DCD267-W	1-25				2-21			1-33			1-33			1-12*	
WattStopper	Paddle	PDMLV-703-W															
WattStopper	Slide	SDMLV-603-W															
WattStopper	Slide	SD-603-W															
Lutron	Skylark	CTCL-153P															
Lutron	Divi	DVCL-153PD		1-3													
Lutron	Divi	DVCL-153P v2 ²		1-3			1-15	16-21					1-8	9-33		1-12*	
Lutron	Divi	DVPCD-203								1-8							
Lutron	Divi	DV-600P		1-25			1-21			1-33			1-33			1-12*	
Lutron	Divi	DV-603PG															
Lutron	DIVA	DVELV-300P	1-13				1-11			1-17			1-17			1-12*	
Lutron	Glyder	GL-600P															
Lutron	Maestro	MACL-153M v2 ²		1-25			1-21			1-33			1-33			1-12*	
Lutron	Maestro	MAELV-600															
Lutron	Maestro	MALV-600															
Lutron	Maestro	MRF2-6ND-120		1-25			1-15	16-21		1-33			1-33			1-12*	
Lutron	Nova	NLV600 ²															
Lutron	Nova	NLV1000 ²		1-25			1-21*			1-33			1-33			1-12*	
Lutron	Nova	NT-600-W															
Lutron	Nova	NTELV-300															
Lutron	Grafik Eye	QSGR-3P ²		1-25			1-21*			1-10			1-10	11-33		1-12*	
Lutron	Qoto	Q-600P															
Lutron	RADIO RA	RRD-6NA ²		1-3						1-15	16-33		1-15	16-33		1-12*	
Lutron	Skylark	S-600P															
Lutron	Skylark	SELV-300P															
Lutron	Skylark	SLV-600P	1-19				1-16			1-25			1-25			1-12*	
Lutron	Skylark	SCL153P v2 ²															
Lutron	Toggler	TG-600P															
Lutron	Credenza	TT-300															
Lutron	Power Module	PHPM-WBX															
Lutron	Verti	VTELV-600M-I															
Lutron	Caseta	PD-6WCL (SD11)		1-3			1-21							X		1-12*	
Sensors																	
Lutron	Maestro	MSCL-OP153MH		1-25			1-21			1-33			1-33			1-12*	1-12*
Lutron	Maestro	MS-OPS2H	1-25				1-21			1-33			1-33			1-12*	
Leviton	Decora	IPS02	1-25				1-21			1-33			1-33			1-12*	
Leviton	Decora	IPS15	1-25				1-21			1-33			1-33			1-12*	
Panel Modules																	
Lutron	Panel Module	GP (Harrier) Card	1-25				1-21*			1-33			1-33				
Lutron	Panel Module	HW/LP-RPM-4U-120		1-25			1-21*			1-33			1-33				

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

WG	Warm Glow
AF	Air Flux
DS	Diamond Spark
CC	Clear Classic
DC	Die Cast
DW	Direct White
SO	Single Optic



6.5W(40W) A19 WG 9290011347(455774); 9290011347(455766); 9290011347(455741); 9290011176(453316); 9290011176(453183)	7W(40W) A19 CC WG 9290011815 (458737, 458752, 458745)	8W A19 409938	8W(40W) A19 Remote Phosphor 417048, 414839	8W(40W) A19 Sultan 9290002267 (423483), 9290002267 (424374), 9290002295 (425256), 9290002267 (429266)
---	--	-----------------------------	--	--

Applicable Philips Part Numbers			# of bulbs			# of bulbs			# of bulbs			# of bulbs			# of bulbs		
Dimmer Company	Brand	Model No.	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Cooper	REACT	RI061-VW-K2							1-16								
Leviton	Decora	6161								X							
Leviton	SureSlide	6613	1-23				1-21			X				X		1-12	>12
Leviton	SureSlide	6615P		1-7*		1-11				X				X	1-9		
Leviton	SureSlide	6631								X							
Leviton	SureSlide	6633	1-23				1-21										
Leviton	SureSlide	6672	1-23				1-21										
Leviton	SureSlide	6674	1-23				1-21		1-14				1-7				X
Leviton	Trimatron	6602	1-23				1-21										
Leviton	Trimatron	6681	1-23				1-21			X	1-4	5-6	>6				X
Leviton	Trimatron	6683								X							
Leviton	Trimatron	6684								X							
Leviton	IllumaTech	IPE04-1LZ							1-16								
Leviton	IllumaTech	IPI06	1-23				1-21		1-16					X		1-9	>9
Leviton	IllumaTech	IPM10	2-23		1	2-21		1									
Leviton	Monet	MNI06-1								X							
Philips	Sunrise	SR1000VA120	2-23		1	2-21		1									
Philips	Sunrise	SR150LED120	1-23			1-21											
Lightolier	Vega	V600VAU							1-2	3-16		1-8			1-13		
Lightolier	Vega	V1000VAU															
Lightolier	Sunrise	ZP600VA ²								X		1-8					X
Lightolier	Sunrise	ZP600								X							
Lightolier	Vega	V600								X							
Lightolier	Onset	OS600							3-16		1 or 2						
Lightolier	Onset	OS600VA							1-4		>4			X	1-13		
Lightolier	Onset	OS1000VA							1-4		>4						
Lightolier	Astral Slider	A600								X							
Lightolier	Astral Slider	AP600								X							
Lightolier	MultiSet	MHP600VA							1-8	9-16			1-16				X
Lightolier	Momentum	MP2000VAI							1-16			1-7					
WattStopper	Micro Decorator	DCD267-W		1-23		2-21		1	1-16					X	2-13 ¹		1
WattStopper	Paddle	PDMLV-703-W															
WattStopper	Slide	SDMLV-603-W															
WattStopper	Slide	SD-603-W															
Lutron	Skylark	CTCL-153P							1-4								
Lutron	Diva	DVCL-153PD						X	1-12			1-8					
Lutron	Diva	DVCL-153P v2 ²			X	1-15	16-21		1-16				1-8		1-18		
Lutron	Diva	DVPDC-203							1-4								
Lutron	Diva	DV-600P	1-23			1-21			1-16					X	1-6		>6
Lutron	Diva	DV-603PG								X				X			
Lutron	DIVA	DVELV-300P	1-7*			1-11			1-9			1-18				1-9	
Lutron	Glyder	GL-600P								X				X			
Lutron	Maestro	MAELV-600		1-23		1-21				X				X	1-12		>12
Lutron	Maestro	MAELV-600							1-16								
Lutron	Maestro	MALV-600								X							
Lutron	Maestro	MRF2-6ND-120	1-23			1-15	16-21			X				X	1-12		>12
Lutron	Nova	NLV600 ²							1-16			1-18			1-8	8-11	>11
Lutron	Nova	NLV1000 ²	1-23*			1-21*			1-16*			1-24*			1-8	8-11	>11
Lutron	Nova	NT-600-W															
Lutron	Nova	NTELV-300															
Lutron	Grafik Eye	QSGR-3P ²	1-23*			1-21*				X				X	1-17		
Lutron	Qoto	Q-600P								X				X			
Lutron	RADIO RA	RRD-6NA ²	1-23					X	1-16			1-16		X	1-13		
Lutron	Skylark	S-600P												X			
Lutron	Skylark	SELV-300P															
Lutron	Skylark	SLV-600P	1-10*			1-16			1-16					X	1-12		>12
Lutron	Skylark	SCL153P v2 ²										1-8			1-18		
Lutron	Toggler	TG-600P															
Lutron	Credenza	TT-300															
Lutron	Power Module	PHPM-WBX							1-32								
Lutron	Verti	VTELV-600M-I															
Lutron	Caseta	PD-6WCL (SD11)	1-23			1-21											
Sensors																	
Lutron	Maestro	MSCL-OP153MH		1-23			1-21								1-18		
Lutron	Maestro	MS-OPS2H	1-23			1-21									1-18		
Leviton	Decora	IPS02	1-23			1-21											
Leviton	Decora	IPS15	1-23			1-21											
Panel Modules																	
Lutron	Panel Module	GP (Harrier) Card				1-21*											
Lutron	Panel Module	HW/LP-RPM-4U-120				1-21*											

¹ Audible noise may be observed when used with this dimmer, depending on the application.
² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

WG	Warm Glow
AF	Air Flux
DS	Diamond Spark
CC	Clear Classic
DC	Die Cast
DW	Direct White
SO	Single Optic



8W
A19 Slim Style



9W(60W)
A19 3000K



9W(60W)
A19 5000K core



9W(60W)
A19 5000K



9W
A19 3000k Core

Applicable Philips Part Numbers			8W A19 Slim Style			9W(60W) A19 3000K			9W(60W) A19 5000K core			9W(60W) A19 5000K			9W A19 3000k Core		
9290002706 (433219); 9290002706 (433136); 9290002704 (433201); 9290002704 (433128)			929001196904 (459057); 929001196905 (462234); 929001196995 (462242)			9290011970 (461327); 9290011970 (455881); 9290011970 (461368); 9290011970 (461335); 9290011970 (461350); 9290011970 (462259)			9290011346 (455881); 9290011346 (455907); 9290011346 (455899); 9290011346 (455873); 9290011177 (453282); 9290011177 (453241);			9290011969 (459057); 9290011969 (462234); 9290011969 (462242)					
Dimmer Company	Brand	Model No.	# of bulbs			# of bulbs			# of bulbs			# of bulbs			# of bulbs		
			Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Cooper	REACT	RI061-VW-K2															
Leviton	Decora	6161															
Leviton	SureSlide	6613	1-18			1-15						1-15			1-15		
Leviton	SureSlide	6615P	1-8				1-8			1-17			1-8			1-8	
Leviton	SureSlide	6631															
Leviton	SureSlide	6633				1-15				1-17			1-15			1-15	
Leviton	SureSlide	6672				1-15				1-17			1-15			1-15	
Leviton	SureSlide	6674	1-18				1-15			1-3		4-17	1-15			1-15	
Leviton	Trimatron	6602				1-15				1-17			1-15			1-15	
Leviton	Trimatron	6681	1-18			1-15				1-17			1-15			1-15	
Leviton	Trimatron	6683															
Leviton	Trimatron	6684															
Leviton	illumatech	IPE04-1LZ															
Leviton	illumatech	IPI06	1-18			1-15				1-17			1-15			1-15	
Leviton	illumatech	IPM10					1-15			1-17			1-15			1-15	
Leviton	Monet	MNI06-1															
Philips	Sunrise	SR1000VA120					1-15			1-17			1-15			1-15	
Philips	Sunrise	SR150LED120					1-15			1-3		4-17	1-15			1-15	
Lightolier	Vega	V600VAU															
Lightolier	Vega	V1000VAU															
Lightolier	Sunrise	ZP600VA ²															
Lightolier	Sunrise	ZP600															
Lightolier	Vega	V600															
Lightolier	Onset	OS600															
Lightolier	Onset	OS600VA															
Lightolier	Onset	OS1000VA															
Lightolier	Astral Slider	A600															
Lightolier	Astral Slider	AP600															
Lightolier	MultiSet	MHP600VA															
Lightolier	Momentum	MP2000VAI															
WattStopper	Micro Decorator	DCD267-W	1-18				1-15			1-17			1-15			1-15	
WattStopper	Paddle	PDMLV-703-W															
WattStopper	Slide	SDMLV-603-W															
WattStopper	Slide	SD-603-W															
Lutron	Skylark	CTCL-153P															
Lutron	Diva	DVCL-153PD									X						X
Lutron	Diva	DVCL-153P v2 ²		1-18				X		1-3	4-17		1-15			1-15	
Lutron	Diva	DVPDC-203															
Lutron	Diva	DV-600P	1-18			1-15				1-17			1-15			1-15	
Lutron	Diva	DV-603PG															
Lutron	DIVA	DVELV-300P	1-8			1-8				1-8			1-8			1-8	
Lutron	Glyder	GL-600P															
Lutron	Maestro	MAEL-153M v2 ²	1-18				1-15			1-3	4-17		1-15			1-15	
Lutron	Maestro	MAELV-600															
Lutron	Maestro	MALV-600															
Lutron	Maestro	MRF2-6ND-120	1-18				1-15			1-17			1-15			1-15	
Lutron	Nova	NLV600 ²															
Lutron	Nova	NLVI000 ²		1-18*		1-15				1-17			1-15*			1-15	
Lutron	Nova	NT-600-W															
Lutron	Nova	NTELV-300															
Lutron	Grafik Eye	QSGR-3P ²	1-18*				1-15			1-3	4-17		1-15*			1-15	
Lutron	Qoto	Q-600P															
Lutron	RADIO RA	RRD-6NA ²	1-18				1-15			1-3	4-17		1-15			1-15	
Lutron	Skylark	S-600P															
Lutron	Skylark	SELV-300P															
Lutron	Skylark	SLV-600P	1-11			1-15				1-13			1-15			1-15	
Lutron	Skylark	SCL153P v2 ²		1-18													
Lutron	Toggler	TG-600P															
Lutron	Credenza	TT-300															
Lutron	Power Module	PHPM-WBX															
Lutron	Verti	VTELV-600M-I															
Lutron	Caseta	PD-6WCL (SD11)					1-15			1-17			1-15			1-15	
Sensors																	
Lutron	Maestro	MSCL-OP153MH								1-17			1-15			1-15	
Lutron	Maestro	MS-OPS2H				1-15				1-17			1-15			1-15	
Leviton	Decora	IPS02				1-15				1-17			1-15			1-15	
Leviton	Decora	IPS15				1-15				1-17			1-15			1-15	
Panel Modules																	
Lutron	Panel Module	GP (Harrier) Card				1-15				1-17			1-15			1-15	
Lutron	Panel Module	HW/LP-RPM-4U-120				1-15				1-17			1-15			1-15	

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

WG	Warm Glow
AF	Air Flux
DS	Diamond Spark
CC	Clear Classic
DC	Die Cast
DW	Direct White
SO	Single Optic



Applicable Philips Part Numbers			9.5W A19 2700K Core			9.5W A19 WG			9.5W A19 2200K-2700K			10W(60W) A19 Clear WG			10W A19 L Prize		
			9290012006 (461269), 9290012006 (461194), 9290012006 (461210), 9290012006 (461244), 9290012006 (461226), 9290012006 (461228), 9290012006 (461251), 9290012006 (461236)			9290011175 (453258); 9290011175 (453324); 929001345 (455865); 929001345 (455857); 929001345 (455840); 929001345 (455831); 929001345 (455832); 929001345 (455816); 9290011175 (453225); 929001345 (455824)			9290011840			9290012149 (462499)			420224, 420075		
Dimmer Company	Brand	Model No.	# of bulbs			# of bulbs			# of bulbs			# of bulbs			# of bulbs		
			Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Cooper	REACT	RI061-VW-K2															X
Leviton	Decora	6161												1-4			
Leviton	SureSlide	6613	1-15			1-15			1-15			1-15			1-5	>5	
Leviton	SureSlide	6615P		1-8		1-8			1-5			1-8			1-4	>4	
Leviton	SureSlide	6631															
Leviton	SureSlide	6633	1-15				1-15		1-15			1-15					
Leviton	SureSlide	6672	1-15			1-15			1-15			1-15					
Leviton	SureSlide	6674		1-15		1-15			1-15			1-15		1	2	>2	
Leviton	Trimatron	6602	1-15			1-15	1-15		1-15			1-15	1-15				
Leviton	Trimatron	6681	1-15			1-15			1-15			1-15	1-15				X
Leviton	Trimatron	6683															
Leviton	Trimatron	6684															
Leviton	IllumaTech	IPE04-1LZ															
Leviton	IllumaTech	IPI06	1-15			1-15			1-15			1-15	1-15		1-2		>2
Leviton	IllumaTech	IPM10		1-15		1-15						1-15					
Leviton	Monet	MNI06-1															
Philips	Sunrise	SR1000VA120		1-15		1-15			1-15			1-15					
Philips	Sunrise	SR150LED120		1-15		1-15			1-15			1-15					
Lightolier	Vega	V600VAU													1-4		
Lightolier	Vega	V1000VAU															
Lightolier	Sunrise	ZP600VA ²												1-10*			
Lightolier	Sunrise	ZP600															
Lightolier	Vega	V600															
Lightolier	Onset	OS600															
Lightolier	Onset	OS600VA												1-4	5-6	>6	
Lightolier	Onset	OS1000VA															
Lightolier	Astral Slider	A600															
Lightolier	Astral Slider	AP600															
Lightolier	MultiSet	MHP600VA												1-9*			
Lightolier	Momentum	MP2000VAI												3-8	1-2		
WattStopper	Micro Decorator	DCD267-W		1-15		1-15			1-15			1-15					
WattStopper	Paddle	PDMLV-703-W															
WattStopper	Slide	SDMLV-603-W															
WattStopper	Slide	SD-603-W															
Lutron	Skylark	CTCL-153P															X
Lutron	Diva	DVCL-153PD			X							1-15			1		>1
Lutron	Diva	DVCL-153P v2 ²		1-15		1-15				X		1-15		1-9*			
Lutron	Diva	DVPDC-203															
Lutron	Diva	DV-600P	1-15			1-15			1-15			1-15		1-4	5	>5	
Lutron	Diva	DV-603PG												1-4	5	>5	
Lutron	DIVA	DVELV-300P	1-8			1-8			1-5			1-8		1-5			
Lutron	Glyder	GL-600P												1-4			
Lutron	Maestro	MACL-153M v2 ²		1-15		1-15				X		1-15		1-9*			
Lutron	Maestro	MAELV-600													1-4		
Lutron	Maestro	MALV-600															X
Lutron	Maestro	MRF2-6ND-120		1-15		1-15			1-15			1-15				1-11*	
Lutron	Nova	NLV600 ²												1-10*			
Lutron	Nova	NLV1000 ²	1-15			1-15*			1-15			1-15		1-10*			
Lutron	Nova	NT-600-W												1-8			
Lutron	Nova	NTELV-300												1-4			
Lutron	Grafik Eye	QSGR-3P ²		1-15		1-15*			1-15			1-15		1-9*			
Lutron	Qoto	Q-600P												1-8		>8	
Lutron	RADIO RA	RRD-6NA ²		1-15		1-15			1-15			1-15		1-9*			
Lutron	Skylark	S-600P															>4
Lutron	Skylark	SELV-300P															
Lutron	Skylark	SLV-600P	1-15			1-15			1-11			1-11			1-4	>4	
Lutron	Skylark	SCL153P v2 ²															
Lutron	Toggler	TG-600P															>6
Lutron	Credenza	TT-300														1-2	
Lutron	Power Module	PHPM-WBX												1-8			
Lutron	Verti	VTELV-600M-I												1-8			
Lutron	Caseta	PD-6WCL (SD11)		1-15		1-15			1-15			1-15					
Sensors																	
Lutron	Maestro	MSCL-OP153MH		1-15		1-15			1-15			1-15					
Lutron	Maestro	MS-OPS2H	1-15			1-15			1-15			1-15					
Leviton	Decora	IPS02	1-15			1-15			1-15			1-15					
Leviton	Decora	IPS15	1-15			1-15			1-15			1-15					
Panel Modules																	
Lutron	Panel Module	GP (Harrier) Card	1-15			1-19			1-15			1-15					
Lutron	Panel Module	HW/LP-RPM-4U-120	1-15						1-15			1-15					

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

WG	Warm Glow
AF	Air Flux
DS	Diamond Spark
CC	Clear Classic
DC	Die Cast
DW	Direct White
SO	Single Optic

10.5W(60W)
A19 Slim style11W(60W)
A19 Sultan12.5W(60W)
A19 Remote Phosphor13W(75W)
A21 Slim style14W(75W)
A21 WG

Applicable Philips Part Numbers			9290002709 (433235); 9290002709 (433151); 9290002707 (433227); 9290002707 (433144);			9290002268 (423491, 424382, 429258); 9290002296 (425264)			409946 (12E26A60-1 and 9290001829 models only)			929001120 (452771), 929001120 (452805), 929001120 (452789), 929001120 (452755), 929001120 (452748), 929001120 (452730)			9290011839(459065), 9290011839(459073), 9290011839(459081), 9290011839(459099)		
Dimmer Company	Brand	Model No.	# of bulbs			# of bulbs			# of bulbs			# of bulbs			# of bulbs		
			Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Cooper	REACT	RI061-VW-K2					1-2 ¹	>3									
Leviton	Decora	6161															
Leviton	SureSlide	6613	1-14				1-13 ¹		1-12			1-13			1-11		
Leviton	SureSlide	6615P		1-5			1-4 ¹	>4	1-12			1-8			1-5		
Leviton	SureSlide	6631													1-11		
Leviton	SureSlide	6633													1-11		
Leviton	SureSlide	6672													1-11		
Leviton	SureSlide	6674	1-14				1-4 ¹	>4	1-12			1-13			1-11		
Leviton	Trimatron	6602													1-11		
Leviton	Trimatron	6681		1-14				X		1-8	>8	1-13			1-11		
Leviton	Trimatron	6683													1-11		
Leviton	Trimatron	6684													1-11		
Leviton	IllumaTech	IPE04-1LZ													1-11		
Leviton	IllumaTech	IPI06	1-14					X	1-12			1-13			1-11	1-11	
Leviton	IllumaTech	IPM10													1-11		
Leviton	Monet	MNI06-1													1-11		
Philips	Sunrise	SR1000VA120													1-11		
Philips	Sunrise	SR150LED120										1-13			1-11		
Lightolier	Vega	V600VAU					1-13 ¹		1-12								
Lightolier	Vega	V1000VAU					1-11* ¹										
Lightolier	Sunrise	ZP600VA ²					1-2 ¹	>2	1-12								
Lightolier	Sunrise	ZP600															
Lightolier	Vega	V600															
Lightolier	Onset	OS600															
Lightolier	Onset	OS600VA					1-13 ¹		1-12								
Lightolier	Onset	OS1000VA															
Lightolier	Astral Slider	A600															
Lightolier	Astral Slider	AP600															
Lightolier	MultiSet	MHP600VA					1-2 ¹	>2	1-12								
Lightolier	Momentum	MP2000VAI															
WattStopper	Micro Decorator	DCD267-W	1-14				1-13 ¹		1-12			1-13			1-11		
WattStopper	Paddle	PDMLV-703-W					1-12 ¹			1-14							
WattStopper	Slide	SDMLV-603-W					1-8 ¹	>8	1-12								
WattStopper	Slide	SD-603-W					1-8 ¹	>8	1-12								
Lutron	Skylark	CTLCL-153P					1-5 ¹	>5									
Lutron	Diva	DVCL-153PD					1-13 ¹										X
Lutron	Diva	DVCL-153P v2 ²		1-14			1-13 ¹		1-12					X	1-11		
Lutron	Diva	DVPCD-203															
Lutron	Diva	DV-600P		1-14			1-4 ¹	>4	1-8	9-12		1-13			1-11		
Lutron	Diva	DV-603PG															
Lutron	DIVA	DVELV-300P	1-5				1-6 ¹		1-12			1-7			1-5		
Lutron	Glyder	GL-600P															
Lutron	Maestro	MACL-153M v2 ²	1-14				1-13 ¹		1-12			1-13				1-11	
Lutron	Maestro	MAELV-600															
Lutron	Maestro	MALV-600															
Lutron	Maestro	MRF2-6ND-120	1-14				1-13 ¹		1-12			1-13			1-11		
Lutron	Nova	NLV600 ²					1-13 ¹		1-12								
Lutron	Nova	NLV1000 ²	1-14*				1-13* ¹		1-16*			1-13*			1-11*		
Lutron	Nova	NT-600-W															
Lutron	Nova	NTELV-300															
Lutron	Grafik Eye	QSGR-3P ²	1-14*				1-13* ¹		1-12*					X	1-11*		
Lutron	Qoto	Q-600P															
Lutron	RADIO RA	RRD-6NA ²		1-14			1-13* ¹		1-12			1-13			1-11		
Lutron	Skylark	S-600P															
Lutron	Skylark	SELV-300P															
Lutron	Skylark	SLV-600P	1-8				1-13 ¹				X	1-10			1-11		
Lutron	Skylark	SCL153P v2 ²	1-14				1-13* ¹							X			
Lutron	Toggler	TG-600P															
Lutron	Credenza	TT-300															
Lutron	Power Module	PHPM-WBX															
Lutron	Verti	VTELV-600M-I															
Lutron	Caseta	PD-6WCL (SD11)														1-11	
Sensors																	
Lutron	Maestro	MSCL-OP153MH										1-13			11*	1-10	
Lutron	Maestro	MS-OPS2H										1-13*			1-11*		
Leviton	Decora	IPSO2										1-13*			1-11*		
Leviton	Decora	IPSI5										1-13*			1-11*		
Panel Modules																	
Lutron	Panel Module	GP (Harrier) Card														1-23	
Lutron	Panel Module	HW/LP-RPM-4U-120														1-23	

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

WG	Warm Glow
AF	Air Flux
DS	Diamond Spark
CC	Clear Classic
DC	Die Cast
DW	Direct White
SO	Single Optic



15W(75W)
A21



17W(75W)
A21 Prince



18W(100W)
A21 WG



19W(100W)
A21



22W(100W)
A21

Applicable Philips Part Numbers			9290002595A (453159), 9290002595A (451898)			17E26A21D (418590), 9290002018 (422220)			9290011741 (459107), 9290011741 (459115), 9290011741 (459123), 9290011741 (459131)			9290002596A (451906)			9290002290(423525), 9290002290(424432)		
Dimmer Company	Brand	Model No.	# of bulbs			# of bulbs			# of bulbs			# of bulbs			# of bulbs		
			Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Cooper	REACT	RI061-VW-K2															X
Leviton	Decora	6161															
Leviton	SureSlide	6613	1-8*				1-8 ¹		1-8				1-6*				X
Leviton	SureSlide	6615P	1-4*				1-4 ¹		1-8				1-3				X
Leviton	SureSlide	6631							1-8								
Leviton	SureSlide	6633							1-8								
Leviton	SureSlide	6672							1-8								
Leviton	SureSlide	6674				X	1-8 ¹		1-8						X		X
Leviton	Trimatron	6602							1-8								
Leviton	Trimatron	6681	1-8*				1-6 ¹	>6	1-8				1-6*				X
Leviton	Trimatron	6683															
Leviton	Trimatron	6684															
Leviton	illumatech	IPE04-ILZ															
Leviton	illumatech	IPI06		1-8*			1-8 ¹		1-8						X		1-6 ¹
Leviton	illumatech	IPM10							1-8								
Leviton	Monet	MNI06-1							1-8								
Philips	Sunrise	SR1000VA120							1-8								
Philips	Sunrise	SR150LED120				X			1-8					X			
Lightolier	Vega	V600VAU					1-5 ¹										X
Lightolier	Vega	V1000VAU															
Lightolier	Sunrise	ZP600VA ²					1-8 ¹										1-6 ¹
Lightolier	Sunrise	ZP600															
Lightolier	Vega	V600															
Lightolier	Onset	OS600															
Lightolier	Onset	OS600VA					1-8 ¹										1-6 ¹
Lightolier	Onset	OS1000VA															
Lightolier	Astral Slider	A600															
Lightolier	Astral Slider	AP600															
Lightolier	MultiSet	MHP600VA					1-8 ¹										1-6 ¹
Lightolier	Momentum	MP2000VAI															
WattStopper	Micro Decorator	DCD267-W	1-8*				1-8 ¹		1-8				1-6*				1-6 ¹
WattStopper	Paddle	PDMLV-703-W															
WattStopper	Slide	SDMLV-603-W															
WattStopper	Slide	SD-603-W															
Lutron	Skylark	CTCL-153P					1-8 ¹										
Lutron	Diva	DVCL-153PD					1-4 ¹				X						X
Lutron	Diva	DVCL-153P v2 ²				X	1-8 ¹		1-8				1-7				X
Lutron	Diva	DVPDC-203						X									
Lutron	Diva	DV-600P	1-8*				1-8 ¹		1-8				1-6*				X
Lutron	Diva	DV-603PG					1-8 ¹										
Lutron	DIVA	DVELV-300P	1-4*				1-4 ¹		1-8				1-3*				X
Lutron	Glyder	GL-600P					1-8 ¹										
Lutron	Maestro	MAELV-600		1-8*			1-8 ¹		1-8				1-6*				1-6 ¹
Lutron	Maestro	MAELV-600															1-6 ¹
Lutron	Maestro	MALV-600															
Lutron	Maestro	MRF2-6ND-120	1-8*				1-8 ¹		1-8				1-6*				1-6 ¹
Lutron	Nova	NLV600 ²					1-8 ¹										1-6 ¹
Lutron	Nova	NLV1000 ²	1-8*				1-14 ¹		1-8*				1-6*				1-10 ¹
Lutron	Nova	NT-600-W															
Lutron	Nova	NTELV-300															
Lutron	Grafik Eye	QSGR-3P ²				X	1-11* ¹		1-8*					X			1-8* ¹
Lutron	Qoto	Q-600P															X
Lutron	RADIO RA	RRD-6NA ²	1-8*				1-8 ¹		1-8				1-7				1-6 ¹
Lutron	Skylark	S-600P					1-8 ¹										
Lutron	Skylark	SELV-300P					1-8 ¹										1-6
Lutron	Skylark	SLV-600P	1-6*				1-4 ¹	>4	1-8				1-4*				1-6 ¹
Lutron	Skylark	SCL153P v2 ²											1-7				
Lutron	Toggle	TG-600P					1-4 ¹	>4									
Lutron	Credenza	TT-300															
Lutron	Power Module	PHPM-WBX															
Lutron	Verti	VTELV-600M-I															
Lutron	Caseta	PD-6WCL (SD11)							1-8								
Sensors																	
Lutron	Maestro	MSCL-OP153MH							1-8*				1-7				
Lutron	Maestro	MS-OPS2H							1-8*								
Leviton	Decora	IPS02							1-8*								
Leviton	Decora	IPS15							1-8*								
Panel Modules																	
Lutron	Panel Module	GP (Harrier) Card							1-22				1-12				
Lutron	Panel Module	HW/LP-RPM-4U-120							1-22				1-17				

¹ Audible noise may be observed when used with this dimmer, depending on the application.
² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

WG	Warm Glow
AF	Air Flux
DS	Diamond Spark
CC	Clear Classic
DC	Die Cast
DW	Direct White
SO	Single Optic



4.5W
PAR16-GU10 WG



4.5W
PAR16-GU10



6W
PAR16-GU10



7W
PAR16-GU10



4.5W
PAR16

Applicable Philips Part Numbers			9290011565(457267); 9290011565(457648); 9290011565(457655)			9290011288(454363), 9290011288(454405), 9290011288(454389), 9290011288(455378)			9000224204(423509); 9290002242(423418); 9290002443(429316)			929001172505(457663)			9290011289(454371), 9290011289(454397), 9290011289(455360)		
Dimmer Company	Brand	Model No.	# of bulbs			# of bulbs			# of bulbs			# of bulbs			# of bulbs		
			Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Cooper	REACT	RI061-VW-K2															
Leviton	Decora	6161															
Leviton	SureSlide	6613	1-20*			1-15			1-16 ¹	>16			X	1-15			
Leviton	SureSlide	6615P	1-20*			1-12			X				X	1-12			
Leviton	SureSlide	6631															
Leviton	SureSlide	6633	1-20*			1-8		9-15				2-16		1-8			
Leviton	SureSlide	6672	1-20*			1-15						2-16		1-15			
Leviton	SureSlide	6674	1-20*			1-15			1-8 ¹	>8		2-13	14-20	1-15			
Leviton	Trimatron	6602	1-20*				1-15						X		1-15		
Leviton	Trimatron	6681	1-20*					X	1-8 ¹	>8			X				
Leviton	Trimatron	6683															
Leviton	Trimatron	6684															
Leviton	IllumaTech	IPE04-1LZ															
Leviton	IllumaTech	IPI06	1-20*			1-15			1-8	>8			X	1-15			
Leviton	IllumaTech	IPM10					2-15	1				2-20			2-15		
Leviton	Monet	MNI06-1															
Philips	Sunrise	SRI000VA120		1-20*		2-15	1					2-20			2-15		
Philips	Sunrise	SRI50LED120	1-20*			1-15						2-13	14-20	1-15			
Lightolier	Vega	V600VAU							1-16 ¹	>16							
Lightolier	Sunrise	ZP600VA							1-25 ¹								
Lightolier	Sunrise	ZP600															
Lightolier	Vega	V600															
Lightolier	Onset	OS600															
Lightolier	Onset	OS600VA							1-8 ¹	>8							
Lightolier	Onset	OS1000VA															
Lightolier	Astral Slider	A600															
Lightolier	Astral Slider	AP600															
Lightolier	MultiSet	MHP600VA							1-8 ¹	>8							
Lightolier	Momentum	MP2000VAI															
WattStopper	Micro Decorator	DCD267-W	1-20*				2-15	1	1-16 ¹	>16		2-16			2-15		
WattStopper	Paddle	PDMLV-703-W															
WattStopper	Slide	SDMLV-603-W															
WattStopper	Slide	SD-603-W															
Lutron	Skylark	CTCL-153P															
Lutron	Diva	DVCL-153PD															
Lutron	Diva	DVCL-153P v2 ²			X			X		X		2-8	9-20				
Lutron	Diva	DVPDC-203										2-20					
Lutron	Diva	DV-600P	1-20*			1-15			1-16 ¹	>16		2-16		1-15			
Lutron	Diva	DV-603PG															
Lutron	DIVA	DVELV-300P	1-20*			1-12			1-12		1-8			1-12			
Lutron	Glyder	GL-600P															
Lutron	Maestro	MACL-153M v2 ²			X			X	1-8 ¹	>8		2-20					
Lutron	Maestro	MAELV-600															
Lutron	Maestro	MALV-600															
Lutron	Maestro	MRF2-600M															
Lutron	Maestro	MRF2-6ND-120			X		1-15		1-25 ¹			2-16		1-15			
Lutron	Nova	NLV600 ²							1-25 ¹								
Lutron	Nova	NLV1000 ²	1-20*			1-15			1-29* ¹				X	1-15			
Lutron	Grafik Eye	QSGR-3P ²	1-20*					X	1-29* ¹			2-20					
Lutron	Qoto	Q-600P															
Lutron	RADIO RA	RRD-6NA ²	1-20*			1-15			1-25			2-16		1-15			
Lutron	Skylark	S-600P															
Lutron	Skylark	SELV-300P															
Lutron	Skylark	SLV-600P	1-20*			1-15			1-8 ¹	>8		2-12		1-15			
Lutron	Skylark	SCL153P v2 ²								X							
Lutron	Toggler	TG-600P															
Lutron	Credenza	TT-300															
Lutron	Credenza	TTCL-100DH															
Lutron	Caseta	PD-6WCL (SD11)		1-20*			1-11					2-16			1-11		
Sensors																	
Lutron	Maestro	MSCL-OP153MH		1-20*			1-15		1-25			2-20		1-15	1-15		
Lutron	Maestro	MS-OPS2H	1-20*			1-15			1-25			2-20		1-15	1-15		
Leviton	Decora	IPS02	1-20*			1-15						2-20		1-15	1-15		
Leviton	Decora	IPS15	1-20*			1-15						2-20		1-15	1-15		
Panel Modules																	
Lutron	Panel Module	GP (Harrier) Card	1-20*									2-20					
Lutron	Panel Module	HW/LP-RPM-4U-120	1-20*									2-20					

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

WG	Warm Glow
AF	Air Flux
DS	Diamond Spark
CC	Clear Classic
DC	Die Cast
DW	Direct White
SO	Single Optic



5W
PAR20 AF



6W
PAR20 AF



6W
PAR20



6W(50W)
PAR20 SO



7W
PAR20

Applicable Philips Part Numbers	929001105 (454256); 929001105 (434976)	9290011448(458919); 9290011452(456111); 9290011451(456103); 9290011450(456095); 9290011449(456087); 9290011448(456079); 9290011447(456061); 9290011446(456053); 9290011445(456046); 9290011487(456269)	929001225403(463620); 929001225004(463646); 929001225104(463653); 929001225204(463661); 929001225304(463679); 929001225404(463687); 929001225504(463695); 929001225904(463703); 929001226004(463711); 929001224704(463729)	929001224704(463729); 929001225004(463646); 929001225104(463653); 929001225204(463661); 929001225304(463679); 929001225305(463604); 929001225335(463844); 929001225403(463620); 929001225404(463687); 929001225405(463612); 929001225435(463851); 929001225465(463794); 929001225605(463638); 929001225635(463869); 929001225904(463703); 929001226004(463711);	410084, 410092, 410100, 417873, 418574,
---------------------------------	--	--	--	---	---

Dimmer Company	Brand	Model No.	# of bulbs			# of bulbs			# of bulbs			# of bulbs			# of bulbs		
			Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Cooper	REACT	RI061-VW-K2															
Leviton	Decora	6161															X
Leviton	SureSlide	6613	1-12*			1-20				X				X			X
Leviton	SureSlide	6615P		1-12*		1-10				1-15			1-15				X
Leviton	SureSlide	6631													3-16	1-2	
Leviton	SureSlide	6633				1-20				1-15			1-15				
Leviton	SureSlide	6672				1-20				1-15			1-15				
Leviton	SureSlide	6674		1-12*		1-20				1-15			1-15		1-16		
Leviton	Trimatron	6602				1-20				1-15			1-15				
Leviton	Trimatron	6681	1-12*			1-20				1-15			1-15		1-4		>4
Leviton	Trimatron	6683													1-4		>4
Leviton	Trimatron	6684															
Leviton	IllumaTech	IPE04-1LZ															X
Leviton	IllumaTech	IPI06			X	1-20			1-15			1-15					X
Leviton	IllumaTech	IPM10						X			X			X			X
Leviton	Monet	MNI06-1						X									X
Philips	Sunrise	SRI000VA120						X			X			X			
Philips	Sunrise	SRI50LED120		1-12*		1-20				1-15			1-15				
Lightolier	Vega	V600VAU													1-16		
Lightolier	Sunrise	ZP600VA													1-16		
Lightolier	Sunrise	ZP600															X
Lightolier	Vega	V600															
Lightolier	Onset	OS600															X
Lightolier	Onset	OS600VA													1-16		
Lightolier	Onset	OS1000VA															X
Lightolier	Astral Slider	A600															X
Lightolier	Astral Slider	AP600															X
Lightolier	MultiSet	MHP600VA													1-16		
Lightolier	Momentum	MP2000VAI													1-16		
WattStopper	Micro Decorator	DCD267-W	1-12*			1-20				1-15			1-15		1-16		
WattStopper	Paddle	PDMLV-703-W													1-6		>6
WattStopper	Slide	SDMLV-603-W															X
WattStopper	Slide	SD-603-W													1-10	11-12	>12
Lutron	Skylark	CTCL-153P															X
Lutron	Diva	DVCL-153PD									X						X
Lutron	Diva	DVCL-153P v2 ²			X			X		1-15				X	1-16		
Lutron	Diva	DVPDC-203											1-15		1-12		
Lutron	Diva	DV-600P		1-12*		1-20				1-15			1-15		1-16		
Lutron	Diva	DV-603PG															X
Lutron	DIVA	DVELV-300P	1-12*			1-10					X			X	3-10		1 or 2
Lutron	Glyder	GL-600P															X
Lutron	Maestro	MACL-153M v2 ²		1-12*		1-20				1-15			1-15				X
Lutron	Maestro	MAELV-600															X
Lutron	Maestro	MALV-600															X
Lutron	Maestro	MRF2-600M															
Lutron	Maestro	MRF2-6ND-120	1-12*					X		1-15			1-15		1-16		
Lutron	Nova	NLV600 ²															
Lutron	Nova	NLV1000 ²	1-12*			1-20*				1-15			1-15		1-16		
Lutron	Grafik Eye	QSGR-3P ²			X	1-20*				1-15			1-15		1-16		
Lutron	Qoto	Q-600P															X
Lutron	RADIO RA	RRD-6NA ²	1-12*			1-20				1-15			1-15		1-16		
Lutron	Skylark	S-600P															X
Lutron	Skylark	SELV-300P															X
Lutron	Skylark	SLV-600P	1-12*			1-20					X			X			X
Lutron	Skylark	SCL153P v2 ²			X												
Lutron	Toggler	TG-600P															X
Lutron	Credenza	TT-300															
Lutron	Credenza	TTCL-100DH															
Lutron	Caseta	PD-6WCL (SD11)						X		1-15			1-15				
Sensors																	
Lutron	Maestro	MSCL-OP153MH				1-20				1-15			1-15				
Lutron	Maestro	MS-OPS2H				1-20*				1-15			1-15				
Leviton	Decora	IPS02				1-20*				1-15			1-15				
Leviton	Decora	IPS15				1-20*				1-15			1-15				
Panel Modules																	
Lutron	Panel Module	GP (Harrier) Card				1-20*											
Lutron	Panel Module	HW/LP-RPM-4U-120				1-20*											

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

WG	Warm Glow
AF	Air Flux
DS	Diamond Spark
CC	Clear Classic
DC	Die Cast
DW	Direct White
SO	Single Optic



12W
Glass PAR30



12W
PAR30L ExpertColor



12.5W
PAR30L SO AF



13W
PAR30L/S AF



11W
PAR38

Applicable Philips Part Numbers

929001294004 (467811),
929001294104 (467829),
929001294204 (467837),
929001294404 (467845),
929001294504 (467852),
929001294604 (467860),
929001294804 (467878),
929001294904 (467886),
929001295004 (467894),
929001295204 (467902),
929001295304 (467910),
929001295404 (467928)

9290012858 (471052), 9290012857
(471045), 9290012856 (471037)

9290011327(454702);
9290011326(454694);
9290011325(454686);
9290011324(454678);
9290011323(454660)

9290002304 (425371); 9290002306
(425397); 9290002302 (425355);
9290002303 (425363); 9290002305
(425389); 9290002284 (423442);
9290002286 (423459); 9290002285
(423467); 9290002287 (423475);
9290002301 (425348); 9290002300
(425330); 9290002233 (420471);
9290002234 (420497); 9290002235
(420505); 9290002244 (420802);
9290002201 (420315); 9290002323
(425298)

9290011120

Dimmer Company	Brand	Model No.	# of bulbs			# of bulbs			# of bulbs			# of bulbs			# of bulbs		
			Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Cooper	REACT	RI061-VW-K2															X
Leviton	Decora	6161															
Leviton	SureSlide	6613		1-13			1-8*							1-11			X
Leviton	SureSlide	6615P		2-5	1		1-5*							1-5			1-7
Leviton	SureSlide	6631															
Leviton	SureSlide	6633		1-13			1-8*			1-8*							X
Leviton	SureSlide	6672				X	1-8*			1-8*							1-14
Leviton	SureSlide	6674				X	1-8*			1-8*			1-11				
Leviton	Trimatron	6602				X	1-8*			1-8*							1-14
Leviton	Trimatron	6681				X	1-8*			1-8*				X			X
Leviton	Trimatron	6683															
Leviton	Trimatron	6684															
Leviton	illumatech	IPE04-1LZ															
Leviton	illumatech	IPI06		1-13			1-8*			1-8*				1-2	>2		1-14
Leviton	illumatech	IPM10		1-16			1-8*			1-8*							1-15
Leviton	Monet	MNI06-1															
Philips	Sunrise	SR1000VA120		1-16			1-8*			1-8*							
Philips	Sunrise	SR150LED120				X	1-8*			1-8*							X
Lightolier	Vega	V600VAU												1-11			
Lightolier	Sunrise	ZP600VA												1-11			
Lightolier	Sunrise	ZP600															
Lightolier	Vega	V600															
Lightolier	Onset	OS600															
Lightolier	Onset	OS600VA												1-8		>8	
Lightolier	Onset	OS1000VA															
Lightolier	Astral Slider	A600															
Lightolier	Astral Slider	AP600															
Lightolier	MultiSet	MHP600VA												1-11			
Lightolier	Momentum	MP2000VAI															
WattStopper	Micro Decorator	DCD267-W				X	1-8*			1-8*				1-11			X
WattStopper	Paddle	PDMLV-703-W															
WattStopper	Slide	SDMLV-603-W															
WattStopper	Slide	SD-603-W															
Lutron	Skylark	CTCL-153P															
Lutron	Diva	DVCL-153PD															
Lutron	Diva	DVCL-153P v2 ²				X	1-8*			1-8*				1-11			X
Lutron	Diva	DVPCD-203				X											
Lutron	Diva	DV-600P		1-13			1-8*			1-8*				1-11			1-14
Lutron	Diva	DV-603PG															
Lutron	DIVA	DVELV-300P		1-5			1-5*			1-5*				1-5			1-7
Lutron	Glyder	GL-600P															
Lutron	Maestro	MACL-153M v2 ²				X	1-8*			1-8*				1-11			X
Lutron	Maestro	MAELV-600															
Lutron	Maestro	MALV-600															
Lutron	Maestro	MRF2-600M												1-11			
Lutron	Maestro	MRF2-6ND-120				X	1-8*			1-8*				1-11			X
Lutron	Nova	NLV600 ²												1-11			
Lutron	Nova	NLV1000 ²		1-13			1-8*			1-8*				1-16*			1-15
Lutron	Grafik Eye	QSGR-3P ²				X				1-8*				1-11*			X
Lutron	Qoto	Q-600P															
Lutron	RADIO RA	RRD-6NA ²				X	1-8*			1-8*				1-11			X
Lutron	Skylark	S-600P															
Lutron	Skylark	SELV-300P															
Lutron	Skylark	SLV-600P		1-9			1-8*			1-8*				1-11			1-10
Lutron	Skylark	SCL153P v2 ²												1-11			
Lutron	Toggler	TG-600P															
Lutron	Credenza	TT-300															
Lutron	Credenza	TTCL-100DH															
Lutron	Caseta	PD-6WCL (SD11)				X	1-8*			1-8*							X
Sensors																	
Lutron	Maestro	MSCL-OP153MH				X	1-8*			1-8*							X
Lutron	Maestro	MS-OPS2H		1-13			1-8*			1-8*							1-15
Leviton	Decora	IPSO2		1-13			1-8*			1-8*							1-15
Leviton	Decora	IPSI5		1-13			1-8*			1-8*							1-15
Panel Modules																	
Lutron	Panel Module	GP (Harrier) Card				X											1-15
Lutron	Panel Module	HW/LP-RPM-4U-120				X											1-15

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

WG	Warm Glow
AF	Air Flux
DS	Diamond Spark
CC	Clear Classic
DC	Die Cast
DW	Direct White
SO	Single Optic



12W
PAR38 SO



13W
PAR38 SO



13.5W
PAR38 GLASS



15W
PAR38



16W
PAR38 Glass

Applicable Philips Part Numbers

9290011834 (460055); 9290011834 (460105); 9290011834 (460071); 9290011835 (460089); 9290011835 (461046); 9290011835 (460097);

9290011322 (454751); 9290011321 (454744); 9290011320 (454736); 9290011319 (454728)

929001292004 (467753), 929001292104 (467761), 929001292204 (467779), 929001292304 (468199), 929001292404 (467787), 929001292504 (467795), 929001292505 (467992), 929001292533 (468017), 929001292604 (467803), 929001292705 (468009), 929001292733 (468025)

92900111104 (453431)

929001291204 (467696), 929001291304 (467704), 929001291404 (467712), 929001291504 (468181), 929001291604 (467720), 929001291703 (467936), 929001291704 (467738), 929001291705 (467976), 929001291804 (467746), 929001291903 (467944), 929001291905 (467984)

Dimmer Company	Brand	Model No.	# of bulbs			# of bulbs			# of bulbs			# of bulbs			# of bulbs		
			Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Cooper	REACT	RI061-VW-K2															
Leviton	Decora	6161															
Leviton	SureSlide	6613			X	1-8*				1-11		1-8*			1-9		
Leviton	SureSlide	6615P		1-7			1-5*			1-5		1-4*			2-5	1	
Leviton	SureSlide	6631															
Leviton	SureSlide	6633			X	1-8*					X	1-8*			1-9		
Leviton	SureSlide	6672		1-14		1-8*				1-11		1-8*		1-9			
Leviton	SureSlide	6674				1-8*					X	1-8*			1-9		
Leviton	Trimatron	6602		1-14		1-8*					X	1-8*		1-9			
Leviton	Trimatron	6681			X	1-8*					X	1-8*		1-9			
Leviton	Trimatron	6683															
Leviton	Trimatron	6684															
Leviton	IllumaTech	IPE04-1LZ															
Leviton	IllumaTech	IPI06		1-14		1-8*				1-11		1-8*		1-9			
Leviton	IllumaTech	IPM10		1-15			1-8*				X	1-8*			1-12		
Leviton	Monet	MNI06-1															
Philips	Sunrise	SR1000VA120					1-8*				X				1-12		
Philips	Sunrise	SR150LED120			X	1-8*					X	1-8*			1-9		
Lightolier	Vega	V600VAU															
Lightolier	Sunrise	ZP600VA															
Lightolier	Sunrise	ZP600															
Lightolier	Vega	V600															
Lightolier	Onset	OS600															
Lightolier	Onset	OS600VA															
Lightolier	Onset	OS1000VA															
Lightolier	Astral Slider	A600															
Lightolier	Astral Slider	AP600															
Lightolier	MultiSet	MHP600VA															
Lightolier	Momentum	MP2000VAI															
WattStopper	Micro Decorator	DCD267-W				X	1-8*				X	1-8*			1-9		
WattStopper	Paddle	PDMLV-703-W															
WattStopper	Slide	SDMLV-603-W															
WattStopper	Slide	SD-603-W															
Lutron	Skylark	CTCL-153P															
Lutron	Diva	DVCL-153PD															
Lutron	Diva	DVCL-153P v2 ²				X	1-8*				X	1-10				X	
Lutron	Diva	DVPDC-203									X					X	
Lutron	Diva	DV-600P	1-14				1-8*				X	1-8*		1-9			
Lutron	Diva	DV-603PG															
Lutron	DIVA	DVELV-300P		1-7			1-5*			1-5		1-4*		1-5			
Lutron	Glyder	GL-600P															
Lutron	Maestro	MAELV-600															
Lutron	Maestro	MALV-600															
Lutron	Maestro	MRF2-600M															
Lutron	Maestro	MRF2-6ND-120				X	1-8*				X	1-8*				X	
Lutron	Nova	NLV600 ²															
Lutron	Nova	NLV1000 ²	1-15				1-8*			1-11		1-8*		1-10			
Lutron	Grafik Eye	QSGR-3P ²				X					X	1-8*				X	
Lutron	Qoto	Q-600P															
Lutron	RADIO RA	RRD-6NA ²				X	1-8*				X	1-10		1-9			
Lutron	Skylark	S-600P															
Lutron	Skylark	SELV-300P															
Lutron	Skylark	SLV-600P		1-10						1-8		1-8*		1-7			
Lutron	Skylark	SCL153P v2 ²															
Lutron	Toggler	TG-600P															
Lutron	Credenza	TT-300															
Lutron	Credenza	TTCL-100DH															
Lutron	Caseta	PD-6WCL (SD11)				X	1-8*				X	1-10				X	
Sensors																	
Lutron	Maestro	MSCL-OP153MH				X	1-8*				X	1-10				X	
Lutron	Maestro	MS-OPS2H	1-15				1-8*			1-11		1-10*		1-9			
Leviton	Decora	IPS02	1-15				1-8*			1-11		1-10*		1-9			
Leviton	Decora	IPS15	1-15				1-8*			1-11		1-10*		1-9			
Panel Modules																	
Lutron	Panel Module	GP (Harrier) Card	1-15								X	1-21		1-10			
Lutron	Panel Module	HW/LP-RPM-4U-120	1-15								X	1-30		1-10			

¹ Audible noise may be observed when used with this dimmer, depending on the application.
² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

WG	Warm Glow
AF	Air Flux
DS	Diamond Spark
CC	Clear Classic
DC	Die Cast
DW	Direct White
SO	Single Optic

PHILIPS



**6W(50W)
BR20 WG**



**8W
BR20 AF**



**9W
BR30**



**9W(65W)
BR30 WG**



**9W
BR30**



**9.5W(65W)
BR30 WG**

Applicable Philips Part Numbers	9290011557 (456979); 9290011557 (456995); 9290011557 (456987)	9290002192 (420331); 9290002192 (423400); 9290002192 (428813)	92900119449 (464180); 929001213763 (461855)	9290011555 (465996); 9290011555 (457044); 9290011555 (457051); 9290011555 (457036); 9290011555 (457077); 9290011555 (457069)	929001174966 (458109); 929001174988 (460352); 929001174989 (465286); 929001174993 (462143); 929001174995 (460345); 929001174997 (464198); 929001174999 (465229);	9290011117 (452243); 929001117 (452235); 929001117 (452268); 929001117 (452284)
---------------------------------	---	---	---	--	--	---

Dimmer Company	Brand	Model No.	# of bulbs			# of bulbs			# of bulbs			# of bulbs			# of bulbs		
			Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Cooper	REACT	RI061-VW-K2															
Leviton	SureSlide	6613		1-25		1-18				1-8			1-16			1-8	1-12*
Leviton	SureSlide	6615P	1-12			1-9				1-8			1-8			1-8	1-7
Leviton	SureSlide	6633		1-25							X		1-16			1-4	5-8
Leviton	SureSlide	6672	1-25						1-8				1-16			1-8	
Leviton	SureSlide	6674		1-25		1-14		>14		1-8			1-16			1-8	1-12*
Leviton	Trimatron	6602	1-25								X		1-16			1-5	6-8
Leviton	Trimatron	6681	1-25			1-8	9-10	>10		1-5	6-8		1-16			1-6	7-8
Leviton	IllumaTech	IPE04-1LZ															
Leviton	IllumaTech	IPI06	1-25				1-18				1-5	6-8	1-16			1-5	6-8
Leviton	IllumaTech	IPM10		2-25	1						1-8		1-16			1-8	
Philips	Sunrise	SR1000VA120		2-25	1						1-8		1-16			1-8	
Philips	Sunrise	SR150LED120		1-25							1-8		1-16			1-8	1-12*
Lightolier	Vega	V600VAU				1-18											
Lightolier	Vega	VI000VAU				1-18											
Lightolier	Sunrise	ZP600VA ²				1-18											
Lightolier	Sunrise	ZP600				1-18											
Lightolier	Onset	OS600				1-18											
Lightolier	Onset	OS600VA				1-8		>8									
Lightolier	Astral Slider	AP600				1-10		>10									
Lightolier	MultiSet	MHP600VA				1-18											
WattStopper	Micro Decoratc	DCD267-W		2-25	1	1-18			1-8				1-16			1-8	1-12*
Lutron	Skylark	CTCL-153P															
Lutron	Diva	DVCL-153PD			X						X			X			
Lutron	Diva	DVCL-153P v2 ²		1-25		1-18					X		1-16			X	1-15
Lutron	Diva	DVPDC-203														X	
Lutron	Diva	DV-600P		1-25		1-8	9-10	>10		1-8	1-8		1-16			1-8	1-12*
Lutron	DIVA	DVELV-300P	1-12					X	1-8			1-8		1-8			1-7
Lutron	Maestro	MACL-153M v2 ²		1-25			1-18 ¹			1-8	1-8		1-16			1-8	1-12*
Lutron	Maestro	MAELV-600															
Lutron	Maestro	MALV-600															
Lutron	Maestro	MRF2-6ND-120		1-25		1-18				1-8			1-16			1-8	1-12*
Lutron	Nova	NLV600 ²				1-18											
Lutron	Nova	NLV1000 ²	1-25*			1-18				1-8		1-16*				1-8	1-12*
Lutron	Nova	NTELV-300															
Lutron	Grafik Eye	QSGR-3P ²		1-15	16-25			X		1-8			1-16*			1-8	1-12*
Lutron	RADIO RA	RRD-6NA ²		1-25		1-18				1-8	1-8		1-16			1-8	1-12*
Lutron	Skylark	SLV-600P		1-15		1-8	9-18		1-8				1-12			1-8	1-7
Lutron	Skylark	SCL153P v2 ²				1-18											1-12*
Lutron	Caseta	PD-6WCL (SD11)		1-15	16-25					1-8			1-16			1-8	1-15
Sensors																	
Lutron	Maestro	MSCL-OP153MH		1-15	16-25	1-18			1-8	1-8			1-16	1-16		1-8	1-12*
Lutron	Maestro	MS-OPS2H	1-25			1-18				1-8			1-16			1-6	1-12*
Leviton	Decora	IPS02	1-25						1-8				1-16			1-8	1-12*
Leviton	Decora	IPS15	1-25						1-8				1-16			1-8	1-12*
Panel Modules																	
Lutron	Panel Module	GP (Harrier) Card	1-25*									1-16*					1-27
Lutron	Panel Module	HW/LP-RPM-4U-120	1-25*									1-16*					1-38

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

WG	Warm Glow
AF	Air Flux
DS	Diamond Spark
CC	Clear Classic
DC	Die Cast
DW	Direct White
SO	Single Optic



**9.5W(65W)
SlimStyle BR30**



**13W
BR30 AF**



**13W
BR30 AF Dim Tone**



**9W(65W)
BR40 WG**



**12W
BR40 AF**



**14.5W
BR40 AF**

Applicable Philips Part Numbers			9290011118 (452359); 9290011118 (452383); 9290011118 (452391); 9290011118 (452417); 9290011119 (452441); 9290011119 (452466); 9290011119 (452482)			9290002197 (420554); 9290002198 (420281); 9290002197 (423798); 9290002197 (429282)			9290002344 (426445)			9290011558 (457010); 9290011558 (457002); 9290011558 (457028)			92900025803 (451914)			9290002199 (420562); 9290002199 (423756)		
Dimmer Company	Brand	Model No.	# of bulbs			# of bulbs			# of bulbs			# of bulbs			# of bulbs			# of bulbs		
			Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Cooper	REACT	RI061-VW-K2								1-11 ¹								1-10		
Leviton	SureSlide	6613	1-8*			1-11				1-11 ¹			1-16		1-10*			1-10		
Leviton	SureSlide	6615P	1-5			1-5				1-5 ¹		1-8	1-16		1-5*				X	
Leviton	SureSlide	6633										1-16	1-16							
Leviton	SureSlide	6672	1-8*									1-16	1-16							
Leviton	SureSlide	6674	1-8*			1-11				1-4 ¹	>4	1-16	1-16		1-10*		1-10			
Leviton	Trimatron	6602										1-16	1-16							
Leviton	Trimatron	6681		1-8*		1-8	>8			1-4 ¹	>4	1-16	1-16		1-5*		1-10			
Leviton	IllumaTech	IPE04-1LZ								1-8 ¹										
Leviton	IllumaTech	IPI06	1-8*			1-11				1-7 ¹	>7	1-16			1-10*		1-10			
Leviton	IllumaTech	IPM10											1-16							
Philips	Sunrise	SR1000VA120											1-16							
Philips	Sunrise	SR150LED120	1-8*										1-16		1-10*					
Lightolier	Vega	V600VAU				1-11				1-11 ¹							1-10			
Lightolier	Vega	VI000VAU				1-16*				1-16* ¹										
Lightolier	Sunrise	ZP600VA ²				1-11				1-5 ¹	>5						1-10			
Lightolier	Sunrise	ZP600					1-5	>5			X									
Lightolier	Onset	OS600						X			X									
Lightolier	Onset	OS600VA				1-11				1-11 ¹							1-10			
Lightolier	Astral Slider	AP600					1-7	>7		1-11 ¹										
Lightolier	MultiSet	MHP600VA				1-11				1-6 ¹	>6						1-10			
WattStopper	Micro Decoratc	DCD267-W	1-8*			1-11				1-11 ¹			1-16		1-10*		1-10			
Lutron	Skylark	CTCL-153P				1-11														
Lutron	Diva	DVCL-153PD					1-11			1-11 ¹				X						
Lutron	Diva	DVCL-153P v2 ²			X	1-11				1-11 ¹			1-16		1-12		1-10			
Lutron	Diva	DVPDC-203								1-11 ¹										
Lutron	Diva	DV-600P		1-8*			1-11			1-5 ¹	>5		1-16		1-10*		1-10			
Lutron	DIVA	DVELV-300P	1-5			1-5				1-5 ¹		1-8			1-5*		1-5			
Lutron	Maestro	MACL-153M v2 ²	1-8*			1-11				1-11 ¹			1-16		1-12		1-10			
Lutron	Maestro	MAELV-600								1-11 ¹										
Lutron	Maestro	MALV-600				1-11				1-11 ¹										
Lutron	Maestro	MRF2-6ND-120	1-8*				1-11			1-11 ¹			1-16		1-10*		1-10			
Lutron	Nova	NLV600 ²				1-11				1-11 ¹							1-10			
Lutron	Nova	NLV1000 ²	1-8*			1-16*				1-16* ¹		1-16*			1-13*		1-10*			
Lutron	Nova	NTELV-300								1-5 ¹										
Lutron	Grafik Eye	QSGR-3P ²			X	1-11*				1-13* ¹			1-16*		1-18*		1-10*			
Lutron	RADIO RA	RRD-6NA ²	1-15			1-11				1-11 ¹			1-16		1-10*		1-10			
Lutron	Skylark	SLV-600P	1-7			1-11				1-11 ¹			1-12		1-8*		1-10			
Lutron	Skylark	SCLI53P v2 ²					1-11 ¹			1-11 ¹					1-12					
Lutron	Caseta	PD-6WCL (SD11)		1-15									1-16		1-12					
Sensors																				
Lutron	Maestro	MSCL-OPI53MH	1-8*										1-16	1-16		1-12				
Lutron	Maestro	MS-OPS2H	1-8*												1-12*					
Leviton	Decora	IPS02	1-8*										1-16		1-12*					
Leviton	Decora	IPS15	1-8*										1-16		1-12*					
Panel Modules																				
Lutron	Panel Module	GP (Harrier) Card	1-26										1-16*		1-18					
Lutron	Panel Module	HW/LP-RPM-4U-120	1-38										1-16*		1-25					

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

WG	Warm Glow
AF	Air Flux
DS	Diamond Spark
CC	Clear Classic
DC	Die Cast
DW	Direct White
SO	Single Optic

PHILIPS



2.5W(25W)
DS



3W



3.5W
Filament



3.5W DW



3.5W (25W) WG DS

Applicable Philips Part Numbers

435149 (9290002799),
451831 (9290011151)

410209, 410217,
420414, 420422,
420430, 426916,
427237

9290012103 (461681)

9290002417 (427799); 9290002419
(427815); 9290002418 (427781);
9290002420 (427807);
9290002417 (427765); 9290002419
(427773);

9290011668 (457242),
9290011668 (457234),
9290011668 (457226)

Dimmer Company	Brand	Model No.	# of bulbs			# of bulbs			# of bulbs			# of bulbs					
			Best	OK	NR	Best	OK	NR	BEST	OK	NR	Best	OK	NR	Best	OK	NR
Cooper	REACT	RI061-VW-K2						X									
Leviton	Decora	6161						X									
Leviton	SureSlide	6613	1-7* ¹					X	1-33			1-35				1-35	
Leviton	SureSlide	6615P			X			X	1-17			1-17				1-17	
Leviton	SureSlide	6631						X									
Leviton	SureSlide	6633		1-7* ¹							1-33					1-25	
Leviton	SureSlide	6672	1-7* ¹								1-33					1-35	
Leviton	SureSlide	6674	1-7* ¹			1-6	7-10	>10		1-10	11-33		1-10 ¹	>10		1-20	
Leviton	Trimatron	6602			X					1-33						1-15*	
Leviton	Trimatron	6681			X			X		1-33				X		1-25	
Leviton	Trimatron	6683						X									
Leviton	IllumaTech	IPE04-1LZ					1-12										
Leviton	IllumaTech	IPI06			X			X		1-33				X		1-35	
Leviton	IllumaTech	IPM10	1-7* ¹							2-33	1					2-25	1
Leviton	Monet	MNI06-1						X									
Philips	Sunrise	SR1000VA120	1-7* ¹							2-33	1					2-25*	1
Philips	Sunrise	SR150LED120	1-7* ¹							1-10	11-33					1-20	
Lightolier	Vega	V600VAU				1-2	3-12								X		
Lightolier	Sunrise	ZP600VA						X					2-42 ¹	1			
Lightolier	Sunrise	ZP600						X									
Lightolier	Vega	V600						X									
Lightolier	Onset	OS600VA					1-4	>4					1-8 ¹	>8			
Lightolier	Onset	OS1000VA					1-4	>4									
Lightolier	Astral Slider	A600						X									
Lightolier	Astral Slider	AP600						X									
Lightolier	MultiSet	MHP600VA				1-12									X		
Lightolier	Momentum	MP2000VAI				1-16											
WattStopper	Micro Decorator	DCD267-W	1-7* ¹			1-12				1-33					X	1-25	
WattStopper	Paddle	PDMLV-703-W						X									
WattStopper	Slide	SDMLV-603-W						X									
WattStopper	Slide	SD-603-W				1-12											
Lutron	Skylark	CTCL-153P						X									
Lutron	Diva	DVCL-153PD						X									
Lutron	Diva	DVCL-153P v2 ²		1-7* ¹			1-12						1-42 ¹				X
Lutron	Diva	DVPDC-203						X		1-8	9-33						
Lutron	Diva	DV-600P		1-7* ¹		1-8			1-33					X		1-15*	
Lutron	Diva	DV-603PG						X									
Lutron	DIVA	DVELV-300P	1-7* ¹				1-2	>2	1-17			10-21	1-10			1-17	
Lutron	Glyder	GL-600P						X									
Lutron	Maestro	MACL-153M v2 ²		1-7* ¹			1-12				1-33			1-42 ¹			1-35
Lutron	Maestro	MAELV-600				1-12											
Lutron	Maestro	MALV-600						X									
Lutron	Maestro	MRF2-600M				1-12											
Lutron	Maestro	MRF2-6ND-120		1-7* ¹				X		1-33			1-42 ¹			1-35	
Lutron	Nova	NLV600 ²				1-12							1-42 ¹				
Lutron	Nova	NLV1000 ²	1-7* ¹			1-20			1-33				1-47* ¹			1-47	
Lutron	Grafik Eye	QSGR-3P ²	1-7* ¹			1-30				1-10	11-33			X		1-50	
Lutron	Qoto	Q-600P						X									
Lutron	RADIO RA	RRD-6NA ²		1-7* ¹		1-12			1-15	16-33		1-42				1-35	
Lutron	Skylark	S-600P						X									
Lutron	Skylark	SELV-300P					1-12										
Lutron	Skylark	SLV-600P	1-7* ¹			1-12				1-25				X	1-15	16-26	
Lutron	Skylark	SCL153P v2 ²						X				4-42 ¹	1-4				
Lutron	Toggle	TG-600P						X									
Lutron	Power Module	PHPM-WBX				1-30											
Lutron	Caseta	PD-6WCL (SD11)	1-7* ¹								X					1-35	
Sensors																	
Lutron	Maestro	MSCL-OP153MH								1-33	1-33					2-45	1
Lutron	Maestro	MS-OPS2H							1-33							1-45	
Leviton	Decora	IPS02							1-33							1-45	
Leviton	Decora	IPS15							1-33							1-35	
Panel Modules																	
Lutron	Panel Module	GP (Harrier) Card	TBD						1-33							1-50*	
Lutron	Panel Module	HW/LP-RPM-4U-120	TBD						1-33							1-50*	

¹ Audible noise may be observed when used with this dimmer, depending on the application.
² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

WG	Warm Glow
AF	Air Flux
DS	Diamond Spark
CC	Clear Classic
DC	Die Cast
DW	Direct White
SO	Single Optic



4.5W(40W)
Filament



4.5W(60W)
Filament



6W(60W)
5000K



6.5W(60W)
DS



7W(60W)
DS WG

Applicable Philips Part Numbers			9290012103 (461681)	929001268735 (465567), 929001268703 (465583), 929001274035 (466235)	929001212735 (461822); 929001212703 (461848)	435180 (9290002886), 452813 (9290011121)	9290011820 (458695); 9290011821 (458661); 9290011822 (458638); 9290011820 (458687); 9290011821 (458653); 9290011822 (458620); 9290011820 (459321); 9290011820 (458703); 9290011821 (458679);
---------------------------------	--	--	---------------------	---	---	---	--

Dimmer Company	Brand	Model No.	# of bulbs			# of bulbs			# of bulbs			# of bulbs			# of bulbs		
			Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Cooper	REACT	RI061-VW-K2															
Leviton	Decora	6161															
Leviton	SureSlide	6613	1-33			1-33				1-25		1-10*		1-21			
Leviton	SureSlide	6615P		1-17			1-17			1-12			X		1-11		
Leviton	SureSlide	6631															
Leviton	SureSlide	6633		1-33			1-33			1-25		1-10*			1-21		
Leviton	SureSlide	6672		1-33			1-33			1-25		1-10*		1-21			
Leviton	SureSlide	6674		1-10	11-33		1-10	11-33		1-25		1-10*			1-21		
Leviton	Trimatron	6602		1-33			1-33			1-25			X		1-21		
Leviton	Trimatron	6681		1-33			1-33			1-25			X	1-21			
Leviton	Trimatron	6683															
Leviton	IllumaTech	IPE04-1LZ															
Leviton	IllumaTech	IPI06		1-33			1-33			1-25			X		1-21		
Leviton	IllumaTech	IPM10		2-33	1		2-33	1		1-25		1-10*			1-25		
Leviton	Monet	MNI06-1															
Philips	Sunrise	SRI000VA120		2-33	1		2-33	1		1-25		1-10*			1-25		
Philips	Sunrise	SRI50LED120		1-10	11-33		1-10	11-33		1-25			1-10*		1-21		
Lightolier	Vega	V600VAU															
Lightolier	Sunrise	ZP600VA															
Lightolier	Sunrise	ZP600															
Lightolier	Vega	V600															
Lightolier	Onset	OS600VA															
Lightolier	Onset	OS1000VA															
Lightolier	Astral Slider	A600															
Lightolier	Astral Slider	AP600															
Lightolier	MultiSet	MHP600VA															
Lightolier	Momentum	MP2000VAI															
WattStopper	Micro Decorator	DCD267-W		1-33			1-33			1-25			1-10*		1-21		
WattStopper	Paddle	PDMLV-703-W															
WattStopper	Slide	SDMLV-603-W															
WattStopper	Slide	SD-603-W															
Lutron	Skylark	CTCL-153P															
Lutron	Diva	DVCL-153PD			X											X	
Lutron	Diva	DVCL-153P v2 ²		1-8	9-33			X			X			X	1-10	11-21	
Lutron	Diva	DVPDC-203					1-8	9-33		1-25							
Lutron	Diva	DV-600P	1-33			1-33			1-25			1-10*			1-21		
Lutron	Diva	DV-603PG															
Lutron	DIVA	DVELV-300P	1-17			1-17			1-12				X		1-11		
Lutron	Glyder	GL-600P															
Lutron	Maestro	MAELV-153M v2 ²		1-33			1-33			1-25			1-10*		1-21		
Lutron	Maestro	MAELV-600															
Lutron	Maestro	MALV-600															
Lutron	Maestro	MRF2-600M															
Lutron	Maestro	MRF2-6ND-120		1-33			1-33			1-25		1-10* ¹			1-21		
Lutron	Nova	NLV600 ²															
Lutron	Nova	NLV1000 ²	1-33			1-33			1-25				1-10* ¹		1-23*		
Lutron	Grafik Eye	QSGR-3P ²		1-10	11-33		1-10	11-33		1-25		1-10*			1-25*		
Lutron	Qoto	Q-600P															
Lutron	RADIO RA	RRD-6NA ²	1-15	16-33		1-15	16-33			1-25			1-10*		1-25		
Lutron	Skylark	S-600P															
Lutron	Skylark	SELV-300P															
Lutron	Skylark	SLV-600P		1-25			1-25			1-25		1-10*		1-16			
Lutron	Skylark	SCL153P v2 ²															
Lutron	Toggle	TG-600P															
Lutron	Power Module	PHPM-WBX															
Lutron	Caseta	PD-6WCL (SD11)			X			X		1-25		1-10*				X	
Sensors																	
Lutron	Maestro	MSCL-OP153MH		1-33			1-33			1-25						X	
Lutron	Maestro	MS-OPS2H	1-33			1-33			1-25					1-21			
Leviton	Decora	IPS02	1-33			1-33			1-25					1-21			
Leviton	Decora	IPS15	1-33			1-33			1-25					1-21			
Panel Modules																	
Lutron	Panel Module	GP (Harrier) Card	1-33			1-33			1-25			1-10*			1-25*		
Lutron	Panel Module	HW/LP-RPM-4U-120	1-33			1-33			1-25			1-10*			1-25*		

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

WG	Warm Glow
AF	Air Flux
DS	Diamond Spark
CC	Clear Classic
DC	Die Cast
DW	Direct White
SO	Single Optic



4W(40W)
WG



4.5W(40W)
2700K



4.5W(40W)
5000K



4.5W(40W)
DS



4.5W(40W)
DS WG

Applicable Philips Part Numbers			469676	929001213763 (461855); 929001213703 (461863); 929001213704 (461871); 929001213765 (461889); 929001213705 (461897); 929001213793 (461905); 929001213863 (461913); 929001213803 (461921); 929001213804 (461939); 929001213865 (461947); 929001213805 (461953); 929001213893 (462358);	929001213003 (463901); 929001213005 (463919); 929001213093 (463943);	435172 (9290002797); 435156 (9290002889); 435164 (9290002798)	9290011673 (457200); 9290011673 (457192); 9290011673 (457184); 9290011674 (457150); 9290011674 (457143); 9290011672 (457176); 9290011672 (457168); 9290011671 (457218); 9290011670 (457135); 9290011670 (457127); 9290011670 (457119);
--	--	--	--------	--	--	---	--

Dimmer Company	Brand	Model No.	# of bulbs			# of bulbs			# of bulbs			# of bulbs			# of bulbs		
			Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Cooper	REACT	RI061-VW-K2															
Leviton	Decora	6161															
Leviton	SureSlide	6613	1-2,4-20		X	2-30			2-30				X	1-26			
Leviton	SureSlide	6615P	1-20			2-16			2-16				X	1-13			
Leviton	SureSlide	6631															
Leviton	SureSlide	6633	2-20		X	2-30			2-30			1-10* ¹		1-26			
Leviton	SureSlide	6672		1-20		2-30			2-30			1-10* ¹		1-26			
Leviton	SureSlide	6674				2-30			2-30			1-10*		1-10*			
Leviton	Trimatron	6602	1,3-20		X	2-30			2-30				X	1-26			
Leviton	Trimatron	6681	1,3-20	2		2-30			2-30				X	1-26			
Leviton	Trimatron	6683															
Leviton	IllumaTech	IPE04-1LZ															
Leviton	IllumaTech	IPI06	1-2,4-20		X	2-30			2-30				X	1-26			
Leviton	IllumaTech	IPM10				2-30			2-30			1-10* ¹		2-32		1	
Leviton	Monet	MNI06-1															
Philips	Sunrise	SR1000VA120		1-20		2-30			2-30			1-10*		2-32		1	
Philips	Sunrise	SR150LED120		1-20		2-30			2-30			1-10*		1-10*			
Lightolier	Vega	V600VAU															
Lightolier	Sunrise	ZP600VA															
Lightolier	Sunrise	ZP600															
Lightolier	Vega	V600															
Lightolier	Onset	OS600VA															
Lightolier	Onset	OS1000VA															
Lightolier	Astral Slider	A600															
Lightolier	Astral Slider	AP600															
Lightolier	MultiSet	MHP600VA															
Lightolier	Momentum	MP2000VAI															
WattStopper	Micro Decorator	DCD267-W		1-20		2-30			2-30			1-10*		1-26			
WattStopper	Paddle	PDMLV-703-W															
WattStopper	Slide	SDMLV-603-W															
WattStopper	Slide	SD-603-W															
Lutron	Skylark	CTCL-153P															
Lutron	Divi	DVCL-153PD		1-20			X			X							
Lutron	Divi	DVCL-153P v2 ²		1-20		2-30			2-30				X			X	
Lutron	Divi	DVPDC-203															
Lutron	Divi	DV-600P	1-20			2-30			2-30				X	1-26			
Lutron	Divi	DV-603PG															
Lutron	DIVA	DVELV-300P	1-20			2-16			2-16				X	1-13			
Lutron	Glyder	GL-600P															
Lutron	Maestro	MAELV-600	1-20			2-30			2-30			1-10*		1-26			
Lutron	Maestro	MAELV-600															
Lutron	Maestro	MRF2-600M															
Lutron	Maestro	MRF2-6ND-120	1-10	15-20		2-30			2-30			1-10*		1-26			
Lutron	Nova	NLV600 ²															
Lutron	Nova	NLV1000 ²	1-20			2-30			2-30			1-10* ¹		1-35			
Lutron	Grafik Eye	QSGR-3P ²	1-20				X			X	1-10*			1-50			
Lutron	Qoto	Q-600P															
Lutron	RADIO RA	RRD-6NA ²	1-20			2-30			2-30			1-10*				X	
Lutron	Skylark	S-600P															
Lutron	Skylark	SELV-300P															
Lutron	Skylark	SLV-600P	1-20			2-30			2-30			1-10*		1-19*			
Lutron	Skylark	SCL153P v2 ²															
Lutron	Toggle	TG-600P															
Lutron	Power Module	PHPM-WBX															
Lutron	Caseta	PD-6WCL (SD11)	3-20		X	2-30				X		1-10*				X	
Sensors																	
Lutron	Maestro	MSCL-OP153MH		1-20		2-30			2-30		X			1-33		1-33	
Lutron	Maestro	MS-OPS2H	1-20			2-30			2-30					1-33			
Leviton	Decora	IPS02	1-20			2-30			2-30					1-26			
Leviton	Decora	IPS15	1-20			2-30			2-30					1-26			
Panel Modules																	
Lutron	Panel Module	GP (Harrier) Card	1-20			2-30			2-30			TBD		1-40*			
Lutron	Panel Module	HW/LP-RPM-4U-120	1-20			2-30			2-30			TBD		1-45*			

¹ Audible noise may be observed when used with this dimmer, depending on the application.
² This dimmer has low end trim adjustment that may be used for optimal performance.




KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

WG	Warm Glow
AF	Air Flux
DS	Diamond Spark
CC	Clear Classic
DC	Die Cast
DW	Direct White
SO	Single Optic

PHILIPS

Applicable Philips Part Numbers			 7W(40W) G25 WG CC Bulb			 10W(60W) G25 WG CC Bulb			 5.5W(40W) Filament ST19		
			9290011817 (458802,458794,458810)			9290011898 (459347); 9290011898 (459339); 9290011816 (458828); 9290011898 (459354); 9290011816 (458844); 9290011816 (458836);			9290012102 (461673)		
Dimmer Company	Brand	Model No.	# of bulbs			# of bulbs			# of bulbs		
			Best	OK	NR	Best	OK	NR	Best	OK	NR
Leviton	SureSlide	6613		1-21			1-15		1-15		
Leviton	SureSlide	6615P	1-11			1-8			1-15		
Leviton	SureSlide	6633		1-21			1-15		1-15		
Leviton	SureSlide	6672	1-21			1-15			1-15		
Leviton	SureSlide	6674	1-21			1-15			1-10		
Leviton	Trimatron	6602	1-21			9-15	1-8		1-25		
Leviton	Trimatron	6681		1-21			1-15		1-15		
Leviton	IllumaTech	IPI06	1-21				1-15		1-25		
Leviton	IllumaTech	IPM10	2-21		1		2-15	1		1-25	
Philips	Sunrise	SR1000VA120	2-21		1		2-15	1		1-25	
Philips	Sunrise	SR150LED120	1-21			1-15			1-10		
WattStopper	Micro Decorator	DCD267-W	2-21		1		1-15		1-15		
Lutron	Diva	DVCL-153PD			X			X			X
Lutron	Diva	DVCL-153P v2 ²	1-15	16-21		1-15					X
Lutron	Diva	DV-600P	1-21				1-15		1-15		
Lutron	DIVA	DVELV-300P	1-11			1-8			1-15		
Lutron	Maestro	MACL-153M v2 ²	1-21				1-15			1-15	
Lutron	Maestro	MRF2-6ND-120	1-15	16-21		1-15			1-15		
Lutron	Nova	NLV1000 ²	1-21*			1-15*			1-15		
Lutron	Grafik Eye	QSGR-3P ²	1-21*			1-15*			1-8		
Lutron	RADIO RA	RRD-6NA ²			X	1-15			1-15		
Lutron	Skylark	SLV-600P	1-16				1-11		1-15		
Lutron	Caseta	PD-6WCL (SD11)	1-21				1-15				X
Sensors											
Lutron	Maestro	MSCL-OP153MH		1-21		11-15	1-10			1-25	
Lutron	Maestro	MS-OPS2H	1-21			1-15			1-25		
Leviton	Decora	IPS02	1-21			1-15			1-25		
Leviton	Decora	IPS15	1-21			1-15			1-25		
Panel Modules											
Lutron	Panel Module	GP (Harrier) Card	1-21*			1-15*			1-15		
Lutron	Panel Module	HW/LP-RPM-4U-120	1-21*			1-15*			1-15		

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

WG	Warm Glow
AF	Air Flux
DS	Diamond Spark
CC	Clear Classic
DC	Die Cast
DW	Direct White
SO	Single Optic