

Essential LED

Essential LED 5-50W 2700K MR16 24D

Essential LED is an affordable LED spot lamp that is suitable for replacing halogen spot lamps. It provides a natural lighting effect as well as instant energy savings – an environmentally friendly solution. The Philips Essential LED family is designed for spot and general lighting applications in the hospitality, retail and home segments.

Product data

General Characteristics

Cap-Base	GU5.3
Bulb	MR16 [MR 16inch/50mm]
Rated Lifetime	15000 hr
(hours)	
Nominal Lifetime	15000 hr
hours	

• Light Technical Characteristics

Color Code Color Designation (text)	827 Warm White
Beam Angle Correlated Color	24 D 2700 K
Temperature Luminous Flux	355 Lm
Luminous Intensity Color rendering	1100 cd 80
index Luminous Efficacy	71.00 l m/W
Lamp	
Color Temperature Rated Luminous Flux	2700 K [CCT 2700K] 355 Lm
LLMF - end nominal lifetime	70 %
Colour consistency Rated Beam Angle	6 steps 24 D

• Electrical Characteristics

Wattage	5 W	
Wattage Technical	5 W	
Voltage	12 V	
Line Frequency	50-60 Hz	
Power Factor	0.5 -	
Lamp Current mA	715 mA	



Dimmable	No
Wattage Equivalent	50 W
Rated Wattage	5.0 W
Starting Time	0.5 (max) s
Warm-up Time to	instant full light
60% Light Outp	Ū.
Suitable for accent	Yes
lighting	

• Temperature Characteristics

• Environmental characteristics

Energy Efficiency A Label (EEL) Energy consumption 6 kWh kWh/1000h

50000X

47.3 mm

49.9 mm

• Measuring Conditions

Switching cycle

• Product Dimensions

Overall Length C Diameter D

• Product Data

Order code Full product code Full product name

Pieces per pack

Order product name

929000237038 929000237038 Essential LED 5-50W 2700K MR16 24D Essential LED 5-50W 2700K MR16 24D 1




Packing configuration	2
Packs per outerbox	2
Bar code on pack -	8
EAN1	
Bar code on	8
outerbox - EAN3	

20 20 8718291680864 8718291680871

Dimensional drawing

0 0

GU5.3



Logistic code(s) -12NC 929000237038 0.035 kg

Net weight per piece

Essential LED 5-50W 2700K MR16 24D

Product	C (Norm)	D (Norm)
LED 5-50W 2700K MR16 24D	47.3	49.9



© 2015 Koninklijke Philips N.V. (Royal Philips) All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting