

MASTER LEDspot PAR

MASTER LEDspot D 14,5-100W 827 PAR38 25D

With its robust design and warm-white beam of light, these newgeneration PAR lamps are ideal for general lighting and spot lighting in the hospitality industry. There is a choice of dimmable and nondimmable versions. They are especially suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 holder and designed for retrofit replacement of halogen/incandescent lamps, MASTER LEDspot PAR deliver huge energy savings and minimize maintenance cost without any reduction in brightness. The IP44-rated outdoor version of the PAR 38 lamp is one of the few energy-saving alternatives to incandescent PAR38 outdoor lamps available today. The dimmable PAR 20 is a perfect replacement for an incandescent spot.

Product data

• General Characteristics

Cap-Base	E27
Bulb	PAR38 [PAR38 mm]
Rated Lifetime	40000 hr
(hours)	
Nominal Lifetime	40000 hr
hours	

• Light Technical Characteristics

Color Code Color Designation (text)	827 Warm White
Beam Angle	25 D
Correlated Color	2700 K
Temperature	
Luminous Flux	900 Lm
Luminous Intensity	4700 cd
Color rendering	80
index	
Luminous Efficacy	62.07 Lm/W
Lamp	
Color Temperature	2700 K [CCT 2700K]
Rated Luminous Flux	900 Lm
LLMF - end nominal	70 %
lifetime	
Colour consistency	6 steps
Rated Beam Angle	25 D
Luminous flux in 90°	900 Lm
cone	

• Electrical Characteristics

Wattage	14.5 W
Wattage Technical	14.5 W
Voltage	220-240 V
Line Frequency	50-60 Hz



Power Factor 0.92 -Lamp Current mA 67 mA Dimmable Yes Wattage Equivalent 100 W Rated Wattage 14.5 W Starting Time 0.5 s instant full light Warm-up Time to 60% Light Outp Suitable for accent Yes lighting

• Temperature Characteristics

• Environmental characteristics

Energy Efficiency	A
Label (EEL)	
Energy consumption	15 kWh
kWh/1000h	

• Measuring Conditions

Switching cycle

- Product Dimensions
- Overall Length C Diameter D

136.4 mm 121.3 mm

50000X

• Product Data

Order code Full product code Full product name 929000259102 929000259102 MASTER LEDspot D 14.5-100W 827 PAR38 25D



MASTER LEDspot PAR

Order product name	MASTER LEDspot D 14.5-100W 827 PAR38 25D
Pieces per pack	1
Packing configuration	10
Packs per outerbox	10
Bar code on pack -	8718291714385
EAN1	

Dimensional drawing

Bar code on outerbox - EAN3 929000259102 Logistic code(s) -12NC Net weight per piece 0.609 kg

8718291714392

D 20 W. C

MASTER LEDspot D 14.5-100W 827 PAR38 25D

Product	C (Norm)	C1 (Max)	D (Norm)	D1 (Norm)
LED D 14.5-100W 827 PAR38 25D	136.4	-	121.3	-



E27



© 2015 Koninklijke Philips N.V. (Royal Philips) All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting