



MASTER LEDtube EM/ Mains

MASTER LEDtube STD 1200mm 14.5W840 T8 I

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. For those that are looking for value for money within limited budget and re-lamping efforts for better light effect and lifetime.

Product data

• General Characteristics

Main Application	Industrial
Cap-Base	G13
Rated Lifetime (hours)	40000 hr
Nominal Lifetime hours	40000 hr

• Light Technical Characteristics

Color Code	840
Beam Angle	150 D
Correlated Color Temperature	4000 K
Luminous Flux	1600 Lm
Color rendering index	83
Rated Luminous Flux	1600 Lm
LLMF - end nominal lifetime	70 %
Colour consistency	6 steps
Rated Beam Angle	150 D

• Electrical Characteristics

Wattage	14.5 W
Voltage	220-240 V
Line Frequency	50/60 Hz
Power Factor	0.9 (min) -
Dimmable	No
Rated Wattage	14.5 W
Starting Time	0.5 (max) s
Warm-up Time to 60% Light Outp	instant full light
Energy saving product	Yes

Suitable for accent lighting	No
------------------------------	----

• Temperature Characteristics

T-case maximum	45 (max) C
Operating temperature	-20 (min), 45 (max) C
T-Storage	-40 (min), 65 (max) C

• Environmental characteristics

Energy Efficiency Label (EEL)	A+
Energy consumption kWh/1000h	14.5 kWh

• Measuring Conditions

Switching cycle	50000X
-----------------	--------

• Product Dimensions

Length A1	1198.0 mm
Fixing Hole Distance A2 Length	1205.0 mm
Length A3	1212.0 mm
Mounting hole diameter	25.68 mm
Circular outline dimension	28 mm

• Approval & Application Chars

VDE marking	No
CE marking	Yes
UL certificate	No



PHILIPS

MASTER LEDtube EM/Mains


RoHS compliance Yes
 KEMA Keur certificate Yes

Pieces per pack 1
 Packing configuration 10
 Packs per outerbox 10
 Bar code on pack - EAN1 8718291793120
 Bar code on outerbox - EAN3 8718291793137
 Logistic code(s) - 12NC 929001119008
 Net weight per piece 0.270 kg

• Product Data


Order code 929001119008
 Full product code 929001119008
 Full product name MASTER LEDtube STD 1200mm 14.5W840 T8 I
 Order product name MST LEDtube STD 1200mm 14.5W840 T8 I

Dimensional drawing




MASTER LEDtube STD 1200mm 14.5W840 T8 I

Product	A1 (Norm)	A2 (Norm)	A3 (Norm)	D1 (Norm)	D2 (Norm)
TLED STD 1200mm 14.5W840 T8 I	1198.0	1205.0	1212.0	25.68	28



G13

Photometric data



STD 1200 mm 14.5 W /840 T8 I



© 2015 Koninklijke Philips N.V. (Royal Philips)
 All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2015, August 29
 data subject to change