



MR16 3W 2700K 24D 9290012397

260 lm


Polar intensity diagram



Cartesian intensity diagram



Beam diagram




Light output ratio 1.00
 Service upward 0.00
 Service downward 1.00

Imax 1094 cd

BS ($1/2 I_{max}$) $2 \times 12^\circ$

BS ($1/2 E_0$) $2 \times 12^\circ$

Visual impact diagram



2016-04-19