



MR16 3W 6500K 24D 9290012398

290 lm


Polar intensity diagram



Cartesian intensity diagram



Beam diagram




Light output ratio 1.00
 Service upward 0.00
 Service downward 1.00

I_{max} 1220 cd

BS (^{1/2}I_{max}) 2 x 12°

BS (^{1/2}E₀) 2 x 12°

Visual impact diagram



2016-04-19