



**MR16 7W 2700K 36D 9290011531**

420lm (90°cone 400lm)


Polar intensity diagram



Cartesian intensity diagram



Beam diagram




Light output ratio 1.00  
 Service upward 0.00  
 Service downward 1.00

Imax 1188 cd

BS ( $\frac{1}{2}l_{max}$ )  $2 \times 16^\circ$

BS ( $\frac{1}{2}E_0$ )  $2 \times 15^\circ$

Visual impact diagram



2016-07-02