



**MR16 7W 4000K 36D 9290011533**

460lm (90°cone 425lm)


Polar intensity diagram



Cartesian intensity diagram



Beam diagram




Light output ratio 1.00  
 Service upward 0.00  
 Service downward 1.00

Imax 1301 cd

BS (1/2Imax) 2 x 16°

BS (1/2E<sub>0</sub>) 2 x 15°

Visual impact diagram



2016-07-02