



Guarantee

2 years



Standards

Bridge

Refer to CE declaration IP bridge on
www.meethue.com/doc

Lamp

Refer to CE declaration of lamp on
www.meethue.com/doc

Lumen output

250 lm @ 4000K

210 lm @ 3000K

145 lm @ 2000K

230 lm @ 6500K

60 lm/W luminous efficacy @4000K

>80 CRI from 2000-4000K

Default start-up (after using wall switch) 195 lm @ 2700K



The bridge

Max. 50 bulbs per bridge

Power consumption – 250mA max

Zigbee Light link protocol 1.0 certified

Frequency band 2400-2483.5MHz

100mm diameter; 25mm height

Desktop or wall mount

4 status LED's

Link button

1 DC input, 1 ethernet port

Factory reset via pinhole

Software upgradable



Power adapter

100-240VAC / 50-60Hz

Output voltage – 5VDC 600mA

Standby power – 0.1W max