

LUMIWARE CANDLES & LUSTRES

SAVE ENERGY WITHOUT COMPROMISING STYLE.

LED filament candles and lustres provide the familiar shape and warm light that customers love, for decorative fixtures that save energy without compromising style.



| Product type | Cap | Type | Lamp Wattage | Replaced Wattage | Lumen | Energy Consumption | Input current | Bulb finish | Voltage | Frequency | 12NC | EOC/6NC |
|----------------------------|-----|------|--------------|------------------|-------|--------------------|---------------|-------------|-----------|-----------|----------|------------|
| LUMIWARE LED | | | W | W | Lm | | mA | | Vac | Hz | 92900199 | 8727900966 |
| 25W E14 835 B35 FR D 1CT10 | E14 | B35 | 2.5 | 25 | 250 | 3 | 15 | Frosted | 220 - 240 | 50/60 | 4062 | 48000 |
| 40W E14 835 B35 FR D 1CT10 | E14 | B35 | 4.5 | 40 | 470 | 5 | 26 | Frosted | 220 - 240 | 50/60 | 4162 | 50300 |
| 25W E14 835 P45 FR D 1CT10 | E14 | P45 | 2.5 | 25 | 250 | 3 | 15 | Frosted | 220 - 240 | 50/60 | 4262 | 52700 |
| 25W E27 835 P45 FR D 1CT10 | E27 | P45 | 2.5 | 25 | 250 | 3 | 15 | Frosted | 220 - 240 | 50/60 | 4362 | 54100 |
| 40W E14 835 P45 FR D 1CT10 | E14 | P45 | 4.5 | 40 | 470 | 5 | 26 | Frosted | 220 - 240 | 50/60 | 4462 | 56500 |
| 40W E27 835 P45 FR D 1CT10 | E27 | P45 | 4.5 | 40 | 470 | 5 | 26 | Frosted | 220 - 240 | 50/60 | 4562 | 58900 |

| | | | |
|---|-------|------------------------------|------|
| CCT | 2700K | Power factor | 0.7 |
| Country of origin | China | Starting time | 0.4 |
| Energy saving product | Yes | Warm up time to 60% light | 0.4 |
| Colour consistency | 6SDCM | Suitable for accent lighting | No |
| Lamp lumen maintenance factor at end of nominal lifetime (=70%) | 70% | Degree of protection (IP) | IP20 |

LUMIWARE CANDLES & LUSTRES

SAVE ENERGY WITHOUT COMPROMISING STYLE.

