

## LUMIWARE SPOTS

PUT THE **ACCENT** ON VALUE.

LED spots are a stylish way to create energy-efficient accents and highlights in a wide range of applications.

**80**  
CRI



**25,000h**

**A+**  
EEI label

**50,000x**

**dimmable**

**10 pack**

Product type	Cap	Type	Lamp Wattage	Replaced Wattage	Lumen	Energy Consumption	MBCP (cd)	Input current	Voltage	Frequency	12NC	EOC/6NC
LUMIWARE LED			W	W	Lm			mA	Vac	Hz	92900199	87279009
GU10 35W 827 36D D 1CT/10	GU10	PAR16	3.6	35	230	4	500	19	220 - 240	50/60	4662	3290066
GU10 50W 827 36D D 1CT/10	GU10	PAR16	5	50	350	5	650	25	220 - 240	50/60	4762	3430066

CCT	2700K
Country of origin	China
Energy saving product	Yes
Colour consistency	6SDCM
Lamp lumen maintenance factor at end of nominal lifetime (=70%)	70%
Power factor	0.7
Starting time	0.4
Warm up time to 60% light	0.4
Suitable for accent lighting	Yes
Degree of protection (IP)	IP00

