


CertaDrive LED 10W 700mA 240V - For Indoor Applications

| 929000832514 | | | | |
|-----------------|--------------------------------------|--|--|--|
| Brand Name | Brand Name PHILIPS LED | | | |
| Description | CertaDrive LED Driver 10W 700mA 240V | | | |
| Input Voltage | 140-280V | | | |
| Input Frequency | 50/60 Hz | | | |

Electrical Specifications

| Input Power | Output | Output | Max T | Output | Max THD | Min | Surge | IP | Application | Weight |
|-------------|---------|---------|---------|--------|---------|--------|------------|----|-------------|--------|
| (W) | current | Voltage | Case | Power | (%) | Power | protection | | | (gm) |
| | (mA) | (V) | (Deg C) | (Max) | | Factor | (KV) | | | |
| 13.0 | 700 | 9 -15 | 70 | 10 | 60 | 0.745 | 1.7 | 20 | Indoor | 45 |

Wiring Diagram LED Driver





Features

| Overvoltage Protection | Shutdown @ 300V |
|--------------------------|-----------------|
| Short circuit Protection | Yes |
| Open circuit protection | Yes |
| LED Reverse protection | Yes |
| Mounting Foot Holes | 70mm |

Dimension Figures

| Dimensions | 80mmx40mmx22mm | | | |
|--------------------------|------------------------|-----------|--|--|
| | | | | |
| Fixing | Suitable for M4 Screws | | | |
| | | | | |
| | Mains | Connector | | |
| Connector(Wire Assembly) | Output | Connector | | |
| | Black | Negative | | |
| | Red | Positive | | |





Philips Electronics India Ltd 9B, DLF 9th Floor DLF Cyber city, DLF phase iii Gurgaon 122002

LED Systems

Lighting