


CertaDrive LED 7W 430mA 240V - For Indoor Applications

929000956414	
Brand Name	PHILIPS LED
Description	CertaDrive LED Driver 7W 430mA 240V
Input Voltage	140-280V
Input Frequency	50/60 Hz

Electrical Specifications

Input Power (W)	Output current (mA)	Output Voltage (V)	Max T Case (Deg C)	Output Power (Max)	Max THD (%)	Min Power Factor	Surge protection (KV)	IP	Application	Weight (gm)
7.0	430	12 - 15	65	5.5	60	0.8	1.7	20	Indoor	45

Wiring Diagram LED Driver



Features

Overvoltage Protection	360V for 2 hours
Short circuit Protection	Yes
Open circuit protection	Yes
LED Reverse protection	Yes
Mounting Foot Holes	70mm

Dimension Figures

Dimensions	80mmx40mmx22mm	
Fixing	Suitable for M4 Screws	
Connector(Wire Assembly)	Mains	Connector
	Output	Connector
	Black	Negative
	Red	Positive

