



Philips myGarden
Wall light

01465
black

myGarden

01465/30/46

Saving energy with ambience

Summon a soft comfortable glow with this Outerstylers wall light. Offering direct and indirect lighting, it creates a smooth and safe passage during those relaxing outdoor moments at night.

Energy saving

- Designed for use with energy-saving light bulbs
- 80% energy saving, compared to traditional light sources

PHILIPS

Wall light
01465 black

Specifications

Design and finishing

- Material: aluminium
- Color: black

Extra feature/accessory incl.

- Waterproof

Product dimensions & weight

- Height: 26 cm
- Length: 18.5 cm
- Width: 10.5 cm
- Net weight: 4.700 kg

Technical specifications

- Mains power: Range 220 V - 240 V, 50 Hz
- Number of bulbs: 1
- Fitting/cap: E27
- Wattage bulb included: bulb not included
- Maximum wattage replacement bulb: 60 W

- Fixture dimmable: No
- LED: No
- IP code: IP44, protection against objects bigger than 1 mm, protection from splashed water
- Class of protection: II - double insulated

Service

- Warranty: 1 year(s)

Packaging dimensions & weight

- Height: 27.8 cm
- Length: 20.3 cm
- Width: 13.3 cm
- Weight: 0.500 kg

Miscellaneous

- Especially designed for: Garden & Patio
- Style: Heritage
- Type: Wall light

014653046

Highlights

80% energy saving



Save up to 80% energy compared to your standard bulb. It pays for itself and saves you money year after year. So reduce your energy bill and start saving Now.

Made for energy-saving bulbs



Philips energy-saving light bulbs conserve energy compared to traditional light sources, helping you to save money on your electricity bills and do your bit for the environment.



Issue date 2015-02-15

Version: 2.2.1

12 NC: 9150 022 38601
EAN: 87 17943 00665 6

© 2015 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com