

Philips myGarden Wall light

01465 white



01465/31/46

Saving energy with ambience

Summon a soft comfortable glow with this Outerstylers wall light. Offering direct and indirect lighting, it creates a smooth and safe passage during those relaxing outdoor moments at night.

Energy saving

- Designed for use with energy-saving light bulbs
- 80% energy saving, compared to traditional light sources



Wall light 01465 white

Specifications

Design and finishing

- Material: aluminium
- · Color: white

Extra feature/accessory incl. Waterproof

Product dimensions & weight

- Height: 26 cm
- Length: 18.5 cm
- Width: 10.5 cm
- Net weight: 4.700 kg

Technical specifications

- Mains power: Range 220 V 240 V, 50 Hz Number of bulbs: 1
- Fitting/cap: E27
- · Wattage bulb included: bulb not included
- Maximum wattage replacement bulb: 60 W

- Fixture dimmable: No
- | FD: No
- IP code: IP44, protection against objects bigger
- than 1 mm, protection from splashed water
- Class of protection: II double insulated

Service

• Warranty: 1 year(s)

Packaging dimensions & weight

- Height: 27.8 cm
- Length: 20.3 cm
- Width: 13.3 cm • Weight: 0.500 kg

Miscellaneous

- Especially designed for: Garden & Patio
- Style: Heritage
- Type: Wall light

014653146

Highlights

80% energy saving



Save up to 80% energy compared to your standard bulb. It pays for itself and saves you money year after year. So reduce your energy bill and start saving Now.

Made for energy-saving bulbs



Philips energy-saving light bulbs conserve energy compared to traditional light sources, helping you to save money on your electricity bills and do your bit for the environment.



© 2015 Koninklijke Philips N.V. Issue date 2015-03-19 All Rights reserved. Version: 2.1.1 Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. or their respective owners. 12 NC: 9150 022 38701 EAN: 87 17943 00666 3

www.philips.com