



Philips myGarden
Wall light

17014
inox

myGarden

17014/47/86



Saving energy with ambience

Summon a soft comforting glow from these smart outdoor lights. The daylight and motion sensor saves energy automatically by turning on only at night, and when motion is detected. Available in different color options.

Energy saving

- Designed for use with energy-saving light bulbs

Premium quality

- Designed for outdoor use - water resistant IP44
- Die-casted aluminum for a premium look and feel

PHILIPS

Wall light
17014 inox

Specifications

Design and finishing

- Material: stainless steel
- Color: inox

Extra feature/accessory incl.

- Motion sensor
- Waterproof

Product dimensions & weight

- Height: 26 cm
- Length: 23.5 cm
- Width: 9.5 cm
- Net weight: 0.475 kg

Technical specifications

- Mains power: Range 220 V - 240 V, 50-60 Hz
- Number of bulbs: 1
- Fitting/cap: E27
- Wattage bulb included: bulb not included

- Maximum wattage replacement bulb: 60 W
- LED: No
- IP code: IP44, protection against objects bigger than 1 mm, protection from splashed water
- Class of protection: II - double insulated

Service

- Warranty: 2 year(s)

Packaging dimensions & weight

- Height: 27.8 cm
- Length: 20.3 cm
- Width: 13.3 cm
- Weight: 0.640 kg

Miscellaneous

- Especially designed for: Garden & Patio
- Style: Contemporary
- Type: Wall light

170144786

Highlights

Made for energy-saving bulbs



Philips energy-saving light bulbs conserve energy compared to traditional light sources, helping you to save money on your electricity bills and do your bit for the environment.

Designed for outdoor use

Designed for outdoor use - water resistant IP44

Premium materials



Die-casted aluminum for a premium look and feel



Issue date 2015-01-19

Version: 1.0.1

12 NC: 9150 001 29808
EAN: 87 17943 76397 9

© 2015 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com