

Philips Ceiling light

31814 65K LED CEILING WHT

12W

white LED

31814/31/66

Essential lighting for a bright home

Essential ceiling lights are designed for flicker free energy saving, high color rendering lamps or LED. Built to resist yellowing and chipping, select models come with add-on rims to complement your décor.

Energy saving

- 80% energy saving
- Built-in LED, as part of the system

Ease of use

· Smooth surface finish for easy cleaning

Light effect

• Even light distribution



Specifications

Design and finishing

· Material: synthetics

· Color: white

Product dimensions & weight

Height: 6.0 cmLength: 29 cmWidth: 29 cmNet weight: 0.545 kg

Technical specifications

• Mains power: Range 110 V - 240 V

• Fixture dimmable: No

LED

• IP code: IP20, protection against objects bigger

than 12.5 mm, no protection against water

• Class of protection: I - earthed

Service

• Warranty: 1 year(s)

Packaging dimensions & weight

Height: 33.4 cmLength: 33.4 cmWidth: 6.7 cmWeight: 0.871 kg

Miscellaneous

· Especially designed for: Functional

• Style: Functional

• Type: Ceiling light

Highlights

Integrated LED light source



A light source you can trust. With integrated LED light source, you won't have to worry about maintenance or lamp replacement while having the perfect light ambiance in your home.

Even light distribution



Even light distribution

80% energy saving



Up to 80% energy saving compared to standard incandescent light sources.

Easy to maintain



Smooth surface finish for easy cleaning



Issue date 2015-03-24

Version: 1.0.1

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. or their respective owners.

12 NC: 9150 044 86901 EAN: 69 47830 42367 5

www.philips.com

All Rights reserved.

© 2015 Koninklijke Philips N.V.