



Philips
Ceiling light

31815 65K LED CEILING WHT
17W
white
LED

31815/31/66

Essential lighting for a bright home

Essential ceiling lights are designed for flicker free energy saving, high color rendering lamps or LED. Built to resist yellowing and chipping, select models come with add-on rims to complement your décor.

Energy saving

- 80% energy saving
- Built-in LED, as part of the system

Ease of use

- Smooth surface finish for easy cleaning

Light effect

- Even light distribution

PHILIPS

Ceiling light
31815 65K LED CEILING WHT 17W white, LED

Specifications

Design and finishing

- Material: synthetics
- Color: white

Product dimensions & weight

- Height: 6.0 cm
- Length: 35 cm
- Width: 35 cm
- Net weight: 0.903 kg

Technical specifications

- Mains power: Range 110 V - 240 V
- Fixture dimmable: No
- LED
- IP code: IP20, protection against objects bigger

- than 12.5 mm, no protection against water
- Class of protection: I - earthed

Service

- Warranty: 1 year(s)

Packaging dimensions & weight

- Height: 39.4 cm
- Length: 39.4 cm
- Width: 6.7 cm
- Weight: 1.317 kg

Miscellaneous

- Especially designed for: Functional
- Style: Functional
- Type: Ceiling light

318153166


Highlights

Integrated LED light source



A light source you can trust. With integrated LED light source, you won't have to worry about maintenance or lamp replacement while having the perfect light ambiance in your home.

Even light distribution



Even light distribution

80% energy saving



Up to 80% energy saving compared to standard incandescent light sources.

Easy to maintain



Smooth surface finish for easy cleaning



Issue date 2015-03-24

Version: 1.0.1

12 NC: 9150 044 87701
EAN: 69 47830 42371 2

© 2015 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com