



Philips
Ceiling light

31817 27K LED CEILING IP65

12W

white
LED

31817/61/66

Quality lighting for a cozy home

This light combines the brightness and durability of LED with the sealed protection of IP65 rating to provide a worry-free solution for hard areas; like the balcony, kitchen and bathroom. You can just simply install and forget about it.

Energy saving

- 80% energy saving

Ease of use

- Smooth surface finish for easy cleaning
- Moisture resistant

Light effect

- Even light distribution

Easy installation

- Easy installation

PHILIPS

Specifications

Design and finishing

- Material: synthetics
- Color: white

Product dimensions & weight

- Height: 29 cm
- Length: 29 cm
- Width: 6.6 cm
- Net weight: 1.027 kg

Technical specifications

- Mains power: Range 110 V - 240 V
- Fixture dimmable: No
- LED
- IP code: IP65, dust tight, protection from jetting

- water
- Class of protection: I - earthed

Service

- Warranty: 1 year(s)

Packaging dimensions & weight


- Height: 33.4 cm
- Length: 33.4 cm
- Width: 7.2 cm
- Weight: 1.330 kg

Miscellaneous

- Especially designed for: Functional
- Style: Functional
- Type: Ceiling light

Highlights

Even light distribution



Even light distribution

Moisture resistant

Moisture resistant

80% energy saving




Up to 80% energy saving compared to standard incandescent light sources.

Easy to maintain



Smooth surface finish for easy cleaning

Easy installation



No more hassle in installation. Just fix or hang securely on the wall and plug in, now this luminaire is ready to light on.



Issue date 2015-03-24

Version: 1.1.1

12 NC: 9150 044 89501
EAN: 69 47830 42382 8

© 2015 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com