



Decorate your home with light

Get your work done in style with this Philips myLiving Cap LED desklight in black. With cool white light for increased efficiency and a flexible neck to direct the light where you need it, this lamp is perfect for any task.

Designed for your home office

- Directed light, perfect for task lighting
- Maximum brightness to light up your workspace

Sustainable light solutions

- High quality LED light
- Energy saving
- Cool white light

Special characteristics

- On/off switch on article
- Flexible arm

Philips myLiving
Table lamp

Cap
white
LED

myLiving



70023/31/16



PHILIPS

Highlights

High quality LED light



The LED technology, integrated into this Philips lamp, is a uniquely developed solution by Philips. While instantly turned on, it enables an optimal light output and brings out vivid colors in your home.

Cool white light




Light can have different color temperatures, indicated in units called Kelvin (K). Lamps with a low Kelvin value produce a warm, more cosy light, while those with a higher Kelvin value produce a cool, more energising light. This Philips light offers cool white light that keeps you energised.

Energy saving




This Philips energy saving lamp conserves energy compared to traditional light sources, helping you to save money on your electricity bills and do your bit for the environment.

Flexible arm



Flexible arm

Maximum brightness



This Philips desk lamp is designed specifically for desk-based activities like doing homework

or browsing the news on the laptop. When you switch it on it immediately provides just the right brightness for maximum comfort.

On/off switch on article



With the button discreetly integrated onto the lamp, you can easily switch the light on and off.

Perfect for task lighting



This Philips desk lamp casts bundled light that provides even illumination on the working area.

Specifications

Design and finishing

- Material: synthetics
- Color: white

Extra feature/accessory incl.

- On/off switch on article
- LED integrated
- Flexible arm
- Rotates freely in any direction

Product dimensions & weight

- Height: 37 cm
- Length: 15.5 cm
- Width: 26 cm
- Net weight: 0.830 kg

Technical specifications

- Mains power: Range 100 V - 240 V, 50-60 Hz
- Bulb technology: LED, DC, MAX 30V
- Number of bulbs: 1
- Wattage bulb included: 3.6 W
- Maximum wattage replacement bulb: 4 W
- Light color: warm white

- Lamp lifetime up to: 20,000 hrs
- Total lumen output fixture: 200 lm
- Fixture dimmable: No
- LED
- Built in LED
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: II - double insulated
- Light source equivalent to traditional bulb of: 37 W

Service

- Warranty: 2 year(s)

Packaging dimensions & weight

- Height: 28.5 cm
- Length: 17.5 cm
- Width: 17.5 cm
- Weight: 1.060 kg

Miscellaneous

- Especially designed for: Home office & Study
- Style: Contemporary
- Type: Table lamp



Issue date 2015-04-15

Version: 2.0.1

12 NC: 9150 049 34601
EAN: 87 18696 12514 4

© 2015 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com