





# Express your style with light

Safe, stylish and easy to fit

Let the elegant designed shade of clean white premium sandblasted glass endears you. Available with Philips bug shield design to keep insects out, you can say goodbye to regular maintenance.

## **Premium quality**

· Carefully hand-crafted material

## **Energy saving**

- · Designed for use with energy-saving light bulbs
- 80% energy saving, compared to traditional light sources

## Ease of use

• Moisture resistant

## **Ambiant light effect**

• Ambient lighting



## Specifications

## Design and finishing

- · Material: glass
- · Color: white

### Extra feature/accessory incl.

Waterproof

## **Product dimensions & weight**

- Height: 12 cm • Length: 26 cm • Width: 26 cm
- Net weight: 1.250 kg

## **Technical specifications**

- Mains power: Range 220 V 240 V, 50-60 Hz
  Number of bulbs: 1
- Fitting/cap: E27
- · Wattage bulb included: bulb not included
- · Maximum wattage replacement bulb: 60 W

- LED: No
- IP code: IP44, protection against objects bigger than 1 mm, protection from splashed water
- Class of protection: I earthed

#### Service

• Warranty: 2 year(s)

## Packaging dimensions & weight

• Height: 32.1 cm • Length: 29.6 cm • Width: 14.3 cm • Weight: 1.328 kg

### **Miscellaneous**

- Especially designed for: Bathroom
- Style: Contemporary
- · Type: Ceiling light

## Highlights

## 80% energy saving

320053176



Save up to 80% energy compared to your standard bulb. It pays for itself and saves you money year after year. So reduce your energy bill and start saving Now.

## Made for energy-saving bulbs



Philips energy-saving light bulbs conserve energy compared to traditional light sources, helping you to save money on your electricity bills and do your bit for the environment.

## **Hand-made materials**

This product is made from a carefully hand-crafted materials to make sure its quality.

## Ambient lighting

Ambient lighting

## **Moisture resistant**

Moisture resistant



Issue date 2015-04-14

© 2015 Koninklijke Philips N.V. All Rights reserved.

Version: 2.1.1

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. or their respective owners.

12 NC: 9150 000 79501 EAN: 87 27900 75078 2

www.philips.com