



Philips myGarden
Wall light

Raccoon
anthracite
LED

myGarden

17273/93/16



Enjoy a beautiful garden with light

Philips myGarden Raccoon wall light in structured anthracite grey lights up outdoor areas powerfully for whatever you like. LED lights, synthetic materials and minimalist design give a contemporary feel to your outdoor space.

Designed for your garden

- IP44 - weather-proof

Sustainable light solutions

- High quality LED light
- Energy saving
- Warm white light
- Long operating life of up to 15 years

PHILIPS

Wall light
Raccoon anthracite, LED


Highlights

High quality LED light



The LED technology integrated into this Philips lamp is a unique solution developed by Philips. It turns on instantly, enables an optimal light output and brings out vivid colours in your home.

Warm white light



Light can have different colour temperatures, indicated in units called Kelvin (K). Lamps with a low Kelvin value produce a warm, more cosy light, while those with a higher Kelvin value produce a cool, more energising light. This Philips lamp offers warm white light for a cosy atmosphere.

Energy saving



This Philips energy-saving lamp conserves energy compared with traditional light sources, helping you

to save money on your electricity bills and do your bit for the environment.

IP44 - weather-proof



This Philips outdoor light is especially designed for humid outdoor environments. It was tested rigorously to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This outdoor light is designed with IP44: it is protected against splashing water. This product is most commonly used and ideal for general outdoor use.

Long operating life



A light source you can trust. The integrated LEDs used in this Philips LED lamp will last up to 15,000 hours (which equals 15 years on the basis of an average use of 3 hours/day with at least 13,000 on/off switching cycles). It feels so good to think that you won't have to worry about maintenance or light bulb replacement while having the perfect light ambience in your home.

172739316

Specifications

Design and finishing

- Material: synthetics, stainless steel
- Colour: anthracite

Extra feature/accessory incl.

- Weatherproof

Product dimensions and weight

- Height: 20.5 cm
- Length: 16.2 cm
- Width: 6.6 cm
- Net weight: 0.540 kg

Technical specifications

- Mains power: Range 220 V–240 V, 50-60 Hz
- Bulb technology: LED, Safety Extra Low Voltage
- Number of bulbs: 1
- Wattage bulb included: 3 W
- Light colour: warm white
- Lamp lifetime up to: 15,000 hrs
- Beam angle: 115°
- Total lumen output fixture: 270 lm
- Fixture dimmable: No
- LED
- Built-in LED
- IP code: IP44, protection against objects bigger than 1 mm, protection from splashed water
- Class of protection: II - double insulated
- Light source equivalent to traditional bulb of: 30 W

Service

- Warranty: 2 year(s)

Packaging dimensions and weight

- Height: 22.8 cm
- Length: 16.3 cm
- Width: 7.8 cm
- Weight: 0.631 kg

Miscellaneous

- Especially designed for: Garden and Patio
- Style: Contemporary
- Type: Wall light



Issue date 2014-08-14

Version: 1.0.1

12 NC: 9150 043 08701
EAN: 87 18291 47946 8

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com