HID-AspiraVision and PrimaVision


AspiraVision is the mark of excellence in HID electronic gear technology – high-end, compact, lightweight and easy to use, with added features for optimal performance of 35, 50 and 70 W CDM lamps. The recently added switching function provides maximum flexibility for users by integrating three different wattage choices into a single driver. PrimaVision Power gear is designed for optimal performance of 100 and 150 W CDM lamps – ideal where high-intensity light is key.

Benefits:

- SOFT START allows installation with fewer circuit breakers; Loop Through (I type) allows faster, cost-efficient installation.
- · Longer lifetime.
- Driver can be set to 35, 50 or 70 W with the integrated switch, which means there is no need to replace the driver if the installation requires lower or higherwattage lamps in the future.
- Optimal lamp performance thanks to minimal lamp power tolerance.
- Eliminates all visible lamp flicker.


Features:

- · Improved thermal performance.
- · Low electromagnetic interference.
- · Voltage drop detection.
- · Lamp end-of-life detection.
- High Tambient and Tcase temperatures.
- Long lifetime of 40,000 hours.



Product ID	Length A1	Fixing Hole Distance Length A2	Width B1	Height C1	Fixing Hole Diameter D1
HID-AV C 35-70 /I CDM	189.2	170.7	83.5	34.7	4.8
HID-PV C 100 & 150 /I CDM	1 224	206	82.7	34.2	4.8

Dimensions in mm



Product ID	Length A1	Fixing Hole Distance Length A2	Width B1	Height C1	Fixing Hole Diameter D1
HID-AV C 35-70 /S CDM	110	98.5	75	32.1	4.5
HID-PV C 100 /S CDM	135	123.5	75	32	4.5
HID-PV C 150 /S CDM	135	123.5	75	32	4.8
Dimensions in mm					

HID-Aspiravision and Primavision								
Shortcode	Description	Wattage (W)	Voltage	Min Order Quantity	Carton Qty			
HIDAVC355070ICDM	HID-AV C 35-70 /I CDM 220-240V 50/60Hz	35/50/70	220-240	1	12			
HIDAVC355070SCDM	HID-AV C 35-70 /S CDM 220-240V 50/60Hz	35/50/70	220-240	1	12			
HIDPVC100ICDM	HID-PV C 100 /I CDM 220-240V SOFT START	100	220-240	10	10			
HIDPVC150ICDM	HID-PV C 150 /I CDM 220-240V 50/60Hz 190	150	220-240	10	10			
HIDPVC100SCDM	HID-PV C 100 /S CDM 220-240V 50/60Hz	100	220-240	10	10			
HIDPVC150SCDM	HID-PV C 150 /S CDM 220-240V 50/60Hz	150	220-240	10	10			