

Philips Ceiling light

31809 CAVANAL LED 40K 18W

WHT

white LED

31809/31/N3

Quality lighting for a cozy home

Philips Cavanal LED Ceiling light is a classic white luminaire that fits into any interior, for energy efficient, high quality and long-lasting light. Choose your desired brightness for different moods at home with step dimming.

Energy saving

- 80% energy saving
- Built-in LED, as part of the system

Ease of use

· Smooth surface finish for easy cleaning

Light effect

• Even light distribution

Advanced LED light

· High light output

Sustainable light solutions

• Extremely long life



Highlights

Integrated LED light source



A light source you can trust. With integrated LED light source, you won't have to worry about maintenance or lamp replacement while having the perfect light ambiance in your home.

Even light distribution



Even light distribution

High light outputHigh quality light with strong light output. The light shines in a beam angle of 40° - the perfect angle for spot lighting.

Extremely long life



Extreme long-life with reliable performance. Philips SmartSpot lighting fixtures are based on high power LED lights that last up to 20.000 Hours, while providing their best light output.

80% energy saving



Up to 80% energy saving compared to standard incandescent light sources.

Easy to maintain



Smooth surface finish for easy cleaning

Specifications

Design and finishing

- · Material: synthetics
- · Color: white

Product dimensions & weight

- Height: 6.7 cm
- Length: 35 cm
- Width: 35 cm
- Net weight: 0.640 kg

Technical specifications

- Mains power: Range 220 V 240 V, 50-60 Hz
- Total lumen output fixture: 1300 lm
- Fixture dimmable
- LED
- Lifetime up to: 20,000 hrs
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- · Class of protection: I earthed

Packaging dimensions & weight

- Height: 39.1 cm
- Length: 38.6 cm
- Width: 7.3 cm
- Weight: 0.937 kg

Miscellaneous

- · Especially designed for: Living- & Bedroom, **Functional**
- · Type: Ceiling light



Issue date 2017-11-09

Version: 1.0.1

12 NC: 9150 055 48101 EAN: 87 18696 16563 8 © 2017 Philips Lighting Holding B.V. All Rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com