

The image shows three Philips LEDtube lamps on a wooden surface. Two are upright, and one is lying on its side. The lamps are white with blue accents and feature the Philips logo and 'LEDtube' text. The background is a blurred wooden surface.

PHILIPS

LEDlamps

LEDtube Standard Output

O LEDtube certo para a melhor eficiência energética

Seja qual for a sua aplicação de iluminação, o portefólio Philips MASTER LEDtube tem o LEDtube certo para si.

Com um fluxo luminoso de 1600lm a 2000lm, o nosso LEDtube Standard Output oferece a melhor eficiência energética com o mais curto retorno do investimento. Uma simples mudança que está disponível em dois comprimentos e temperaturas de cor, com a opção de casquilhos rotativos.

A escolha certa para parques de estacionamento, transportes públicos e armazéns.



Dados de produto

MASTER LEDtube Standard Output



4000/6500



G13



ROTATIVO (ROT)



NÃO REGULÁVEL



40,000 H



EEL




160°
ÂNGULO ABERTURA



27.3 | 1198 | 1498
DIMENSÕES



EM



HF

Tipo de produto	LED	Tradicional	Casquilho rotativo	Fluxo luminoso	Operação	Ângulo abertura	IRC	Temperatura de cor	EOC 1 pcs (C)*
MASTER LEDtube	Potência	Equivalente		Lumen		°		K	
1200mm ROT	14,5 W	36 W	Sim	1600 lm	EM & 230V	160°	83	4000	871829179308300
1200mm ROT	14,5 W	36 W	Sim	1600 lm	EM & 230V	160°	83	6500	871829179310600
1500mm	20 W	58 W	Não	2000 lm	EM & 230V	160°	83	4000	871829173451200
1500mm	20 W	58 W	Não	2000 lm	EM & 230V	160°	83	6500	871829173453600
1200mm InstantFit	16,5 W	36 W	Não	1600 lm	HF	160°	83	4000	871829172885600
1200mm InstantFit	16,5 W	36 W	Não	1600 lm	HF	160°	83	6500	871829172887000
1500mm ROT InstantFit	22 W	58 W	Sim	2000 lm	HF	160°	83	4000	871869640078400
1500mm ROT InstantFit	22 W	58 W	Sim	2000 lm	HF	160°	83	6500	871869640080700

