



Tornado T2

TornadoT2 8y 20W CDL E27 220-240V 1CT/12

Tornado has outstanding brightness which makes your colors appear more Vivid. It fits everywhere due to its compact design. With comprehensive product range, it allows easy replacement of incandescent lamps all the way.


Product data

General Information		Lamp Current (Nom)	
Cap-Base	E27 [E27]		150 mA
Bulb Shape	Spiral	Wattage Equivalent	88 W
Nominal Lifetime (Nom)	8000 h	Starting Time (Nom)	0.3 s
Switching Cycle	5000X	Warm Up Time To 60% Light (Min)	5 s
		Warm Up Time To 60% Light (Max)	60 s
		Power Factor (Nom)	0.6
		Voltage (Nom)	220-240 V
Light Technical		Controls and Dimming	
Color Code	865 [CCT of 6500K]	Dimmable	No
Luminous Flux (Nom)	1200 lm		
Luminous Flux (Rated) (Nom)	1200 lm	Approval and Application	
Color Designation	Cool Daylight	Energy Efficiency Label (EEL)	A
Lumen Maintenance 2000 h (Nom)	85 %	Mercury (Hg) Content (Nom)	1.5 mg
Lumen Maintenance 5000 h (Nom)	75 %	Energy Consumption kWh/1000 h	20 kWh
Chromaticity Coordinate X (Nom)	313	Product Data	
Chromaticity Coordinate Y (Nom)	337	Full product code	871829166294500
Correlated Color Temperature (Nom)	6500 K	Order product name	TornadoT2 8y 20W CDL E27 220-240V 1CT/12
Luminous Efficacy (rated) (Nom)	61 lm/W	EAN/UPC - Product	8718291662945
Color Rendering Index (Nom)	80	Order code	929689848410
LLMF At End Of Nominal Lifetime (Nom)	70 %	Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	12
Operating and Electrical			
Input Frequency	50 or 60 Hz		
Power (Rated) (Nom)	20 W		

Tornado T2

Material Nr. (12NC)	929689848410
Net Weight (Piece)	0.065 kg

Dimensional drawing



Product	D	C	F
TornadoT2 8y 20W CDL E27 220-240V 1CT/12	56.5 mm	111.5 mm	47 mm

QSPIR-F 20W/865 E27 220-240V 50/60Hz

