



Tornado High Lumen

Tornado High Lumen 45W WW E27 1CT/6


Energy saving lamp in spiral shape, with superior performance (long life, high switching) and high lumen warm bright light. Perfectly suitable to be used in places where high lumen is required, and the lamp is directly visible.

Product data

General Information		Wattage Equivalent	
Cap-Base	E27 [E27]		198 W
Bulb Shape	Spiral	Starting Time (Nom)	1.5 s
Nominal Lifetime (Nom)	10000 h	Warm Up Time To 60% Light (Max)	60 s
Switching Cycle	10000X	Power Factor (Nom)	0.92
		Voltage (Nom)	220-240 V
Light Technical		Controls and Dimming	
Color Code	827 [CCT of 2700K]	Dimmable	No
Luminous Flux (Nom)	3080 lm		
Luminous Flux (Rated) (Nom)	3080 lm	Approval and Application	
Color Designation	Warm White (WW)	Energy Efficiency Label (EEL)	A
Lumen Maintenance 2000 h (Nom)	88 %	Mercury (Hg) Content (Max)	3.5 mg
Chromaticity Coordinate X (Nom)	463	Energy Consumption kWh/1000 h	45 kWh
Chromaticity Coordinate Y (Nom)	420	Product Data	
Correlated Color Temperature (Nom)	2700 K	Full product code	872790080822300
Luminous Efficacy (rated) (Nom)	68.38 lm/W	Order product name	Tornado High Lumen 45W WW E27 1CT/6
Color Rendering Index (Nom)	80	EAN/UPC - Product	8727900808223
LLMF At End Of Nominal Lifetime (Nom)	60 %	Order code	929676005701
Operating and Electrical		Numerator - Quantity Per Pack	1
Input Frequency	50 or 60 Hz	Numerator - Packs per outer box	6
Power (Rated) (Nom)	45.0 W	Material Nr. (12NC)	929676005701
Lamp Current (Nom)	190 mA	Net Weight (Piece)	0.270 kg

Tornado High Lumen

Dimensional drawing



Product	C (max)	F	D (max)
Tornado High Lumen 45W WW E27 1CT/6	244 mm	88.1 mm	102 mm

HL HS HV 10Kh EMI HPF 45W 220-240V E27WW

