



Accentline

Accent KSA 50W GU5.3 12V 36D ICT/I0X5F

Low-voltage halogen burner in glass reflector. Ideal solution for small decorative luminaires, putting your objects in the spotlight. Dichroic coating prevents heat transmission onto the object.

Product data

• General Information

Cap-Base	GU5.3 [GU5.3]
Bulb Shape	MR16 [2inch/50mm]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life To 50% Failures (Nom)	4000 h
Nominal Lifetime (Nom)	4000 h
Switching Cycle	16000X

• Light Technical

Beam Angle (Nom)	36 °
Luminous Flux (Nom)	680 lm
Luminous Intensity (Max)	1500 cd
Correlated Color Temperature (Nom)	3000 K
Color Rendering Index (Nom)	100
Luminous Flux In 90° Cone (Rated)	680 lm

• Operating and Electrical

Power (Rated) (Nom)	50 W
---------------------	------

Starting Time (Nom)	0.0 s
Warm Up Time To 60% Light (Nom)	instant full light s
Voltage (Nom)	12 V

• Controls and Dimming

Dimmable	Yes
----------	-----

• Approval and Application


Energy Efficiency Label (EEL)	B
Energy Consumption kWh/1000 h	53 kWh

• Product Data

Full product code	871869670027300
Order product name	Accent KSA 50W GU5.3 12V 36D ICT/I0X5F
Order code	925721917102
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	50
Material Nr. (12NC)	925721917102
Net Weight (Piece)	0.006 kg

PHILIPS

Dimensional drawing




GU5.3, MR16

MR16 4000h 12V 50W 36D GU5.3

Product	D	C
Accent KSA 50W GU5.3 12V 36D ICT/10XSF	51 mm	46 mm

Photometric data



© 2016 Philips Lighting Holding B.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2016, Oct 1
data subject to change