

## A cost effective option for everyday lighting applications

The new Philips LED family delivers LED benefits at an extremely affordable price. With lifetimes 10 times longer than incandescents, instant-on light and an inviting lighting effect, these LEDs are a great replacement for the incandescents, halogens, and CFLs you use every day.\*

## LED replacements for many applications

- · Traditional lamp shapes (A19, BR30 & PAR38)
- Similar light output to the most popular conventional wattages:\*\*
  - 60W & 100W A19
  - 65W BR30
  - 90W PAR38
- · LED linear T8 replacement with 36,000 hour rated life

- · Available in a range of color temperatures
  - 2700K (A19, BR30)
  - 3000K (PAR38)
- 10,950 hour rated life<sup>1</sup>
- BR30 dims smoothly to <10%
- · A19 LED lamps provide all-around light

## Ordering, Electrical and Technical Data (Subject to change without notice)

Grainger Number	Model Number	Ordering Code	Description	Lamp Type	Base	Nom. Watts	Rated Life <sup>1</sup>	Approx. Lumens <sup>2</sup>	CRI	Color Temp (K)		
Standard Incandescent A19 60W Equivalent												
40CP58	9290011750	8.5A19/LED/827 ND 120V	60W Non-Dim	A19	E26	8.5	10,950	800	>80	2700		
Standard Incandescent A19 100W Equivalent												
40CP59	9290011349	14.5A19/LED/827 ND 120V	100W Non-Dim	A19	E26	14.5	10,950	1500	>80	2700		
Standard Incandescent BR30 65W Dimmable Equivalent												
40CP60	9290011749	8BR30/LED/827/DIM 120V	65W Dim	BR30	E26	8	10,950	650	>80	2700		
Standard Incandescent PAR38 90W Equivalent												
40CP57	9290011747	11PAR38/F25/830 ND 120V	90W Non-Dim	PAR38	E26	11	10,950	950	>80	3000		
LED Instant	Fit T8 - 4' Glas	s										
40CP62	9290011511	17T8/48-4000 IFG 10/1	20W Non-Dim	TLED	G13	20.0	36,000	2100	82	4000		
40CP61	9290011512	17T8/48-5000 IFG 10/1	20W Non-Dim	TLED	G13	20.0	36,000	2100	82	5000		

- 1. Rated average life based on engineering testing and probability analysis.
- 2. Based on photometric testing consistent with IES LM-79.

Footnotes from front:

- \* When compared to a 1000 hour A19 incandescent, the 10,950 hour LED A19 lamp has more than 10 times the life.
- \*\* The 8.5W LED A19 lamps produce 800 lumens as compared to the 800 lumens produced by a 60W incandescent. The 14W and 14.5W LED A19 lamps produce 1500 lumens as compared to the 1600 lumens produced by a 100W incandescent. The 8W LED BR30 produces 650 lumens as compared to the 650 lumens produced by a 65W incandescent. The 11W LED PAR38 produces 4085 cd (candela) as compared to the 3698 cd produced by a 90W halogen.

## Shipping Data (Subject to change without notice)

Product Number	SKU UPC (0-46677)	Outer Bar Code (5-00-46677)	Case Qty.	Case Weight (lbs.)	Case Cube (cu. Ft.)	Pallet Qty	SKUs per Layer	Layers High	SKU Dimensions (W x D x H) (In.)	Case Dimensions (W x D x H) (In.)	Pallet Dimensions (W x D x H) (In.)
Standard Incandescent A19 60W Equivalent											
45809-1	45809-6	45809-1	6	3.84	0.124	1764	252	7	2.5 x 2.5 x 4.4	7.8 x 5.4 x 5.1	47.2 x 39.4 x 41.5
Standard Incandescent A19 100W Equivalent											
45568-3	45568-2	45568-7	6	3.84	0.124	1764	252	7	2.5 x 2.5 x 4.4	7.8 x 5.4 x 5.1	47.2 x 39.4 x 41.5
Standard	Standard Incandescent BR30 65W Dimmable Equivalent										
45810-9	45810-2	45810-7	6	2.99	0.423	450	90	5	4.1 x 4.1 x 5.7	13 x 8.8 x 6.4	47.2 x 39.4 x 37.8
Standard Incandescent PAR38 90W Equivalent											
45799-3	45799-0	45799-5	6	10.6	0.641	270	54	5	5.2 x 5.2 x 5.8	15.9 x 10.8 x 6.4	47.2 x 39.4 x 38
LED InstantFit T8 - 4' Glass											
40CP62	45656-6	45656-1	10	4.6	.59	600	60	10	1.1 x 1.1 x 48.0	48.8 x 6.0 x 3.5	49.2 x 39.4 x 40.9
40CP61	45657-3	45657-8	10	4.6	.59	600	60	10	1.1 x 1.1 x 48.0	48.8 x 6.0 x 3.5	49.2 x 39.4 x 40.9

For more information, contact your Grainger Representative or visit www.grainger.com®





© 2015 Koninklijke Philips N.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.



