

11/6/2019

Information as of this date. Please check the DLC QPL for confirmation (www.designlights.org/QPL).

Product Id	Model No.	Classification
PFK43H9F	FSI430L830-347-DIM-(_LSXR10, DAYOCC, SWZDT, IAP)	standard
PIYHDLZZ	FSI430L830-UNV-DIM-(_LSXR10, DAYOCC, SWZDT, IAP)	standard
P78DLOWH	FSI430L835-347-DIM-(_LSXR10, DAYOCC, SWZDT, IAP)	standard
PGLL49H7	FSI430L835-UNV-DIM-(_LSXR10, DAYOCC, SWZDT, IAP)	standard
POP79DQY	FSI430L840-347-DIM-(_LSXR10, DAYOCC, SWZDT, IAP)	standard
PCZXG7K8	FSI430L840-UNV-DIM-(_LSXR10, DAYOCC, SWZDT, IAP)	standard
PJL4JQG3	FSI430L850-347-DIM-(_LSXR10, DAYOCC, SWZDT, IAP)	standard
PPUJ8S66	FSI430L850-UNV-DIM-(_LSXR10, DAYOCC, SWZDT, IAP)	standard
P9YXKWZZ	FSI440L830-347-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PN8DXAHM	FSI440L830-UNV-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
P8CFP3F3	FSI440L830-UNV-DIM-EMLED	standard
P9ZPQYYS	FSI440L835-(UNV347)-DIM-EMLED	standard
P935CTTJ	FSI440L835-347-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PK46UZZA	FSI440L835-UNV-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PDGCKUK9	FSI440L840-(UNV347)-DIM-EMLED	standard
PE8C9SXB	FSI440L840-347-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PHNTFNZP	FSI440L840-UNV-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PSNPNAW4	FSI440L850-(UNV347)-DIM-EMLED	standard
PP28DSMC	FSI440L850-347-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
P63HDFQ8	FSI440L850-UNV-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PAECKGC7	FSI455L830-(UNV347)-DIM-EMLED	standard
P5Z8UZFA	FSI455L830-(UNV347)-DIM-EMLED	standard
PUKCFJR2	FSI455L830-347-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PFE59M9X	FSI455L830-347-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PSKDENSN	FSI455L830-UNV-(DIMXDIMSDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
P52CA6H5	FSI455L830-UNV-(DIMXDIMSDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PF95BN4Z	FSI455L835-(UNV347)-DIM-EMLED	standard
PK55SK13	FSI455L835-(UNV347)-DIM-EMLED	standard
PXHAVHHW	FSI455L835-347-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PWFVYMNU	FSI455L835-347-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PBMG1FCY	FSI455L835-UNV-(DIMXDIMSDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PS49D5Z7	FSI455L835-UNV-(DIMXDIMSDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PR3FHAEJ	FSI455L840-(UNV347)-DIM-EMLED	standard
PPED8S4H	FSI455L840-(UNV347)-DIM-EMLED	standard
PMMY4J9M	FSI455L840-347-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PXQRUNP6	FSI455L840-347-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
P6B185K5	FSI455L840-UNV-(DIMXDIMSDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PP13TCMP	FSI455L840-UNV-(DIMXDIMSDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PWJMKHWN	FSI455L850-(UNV347)-DIM-EMLED	standard
PFVM1EY8	FSI455L850-(UNV347)-DIM-EMLED	standard
PQDY4NBT	FSI455L850-347-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
P6XAPSXG	FSI455L850-347-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PRQ88N7B	FSI455L850-UNV-(DIMXDIMSDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
P8EDST4Y	FSI455L850-UNV-(DIMXDIMSDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PFXWEMYH	FSI470L830-347-DIM-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PTCDBFR4	FSI470L830-347-DIM-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PYSQXC2B	FSI470L830-UNV-DIM-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
P1EAD6FA	FSI470L830-UNV-DIM-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PTNCGPVF	FSI470L830-UNV-DIM-EMLED	standard
PSAJVSF8	FSI470L830-UNV-DIM-EMLED	standard
PEMRYG6B	FSI470L835-347-DIM-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PTP9VS3E	FSI470L835-347-DIM-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PSGZ9GDU	FSI470L835-UNV-DIM-(_LSXR10 DAYOCC, SWZDT, IAP)	standard

11/6/2019

Information as of this date. Please check the DLC QPL for confirmation (www.designlights.org/QPL).

Product Id	Model No.	Classification
P26YE4MX	FSI470L835-UNV-DIM-(_LSXR10 DAYOCC,SWZDT,IAP)	standard
P279SNVA	FSI470L835-UNV-DIM-EMLED	standard
PC5RZK6P	FSI470L835-UNV-DIM-EMLED	standard
PNHK6HE2	FSI470L840-347-DIM-(_LSXR10 DAYOCC,SWZDT,IAP)	standard
PUHRXQWQ	FSI470L840-347-DIM-(_LSXR10 DAYOCC,SWZDT,IAP)	standard
PWJAAP3X	FSI470L840-UNV-DIM-(_LSXR10 DAYOCC,SWZDT,IAP)	standard
PEPHGRW8	FSI470L840-UNV-DIM-(_LSXR10 DAYOCC,SWZDT,IAP)	standard
PR9CDGE9	FSI470L840-UNV-DIM-EMLED	standard
P7GR1JCS	FSI470L840-UNV-DIM-EMLED	standard
PJ76FYYW	FSI470L850-347-DIM-(_LSXR10 DAYOCC,SWZDT,IAP)	standard
PF8MHSGE	FSI470L850-347-DIM-(_LSXR10 DAYOCC,SWZDT,IAP)	standard
PVRY7C2G	FSI470L850-UNV-DIM-(_LSXR10 DAYOCC,SWZDT,IAP)	standard
PZT589W3	FSI470L850-UNV-DIM-(_LSXR10 DAYOCC,SWZDT,IAP)	standard
P3W9EPU2	FSI470L850-UNV-DIM-EMLED	standard
PB96ET72	FSI470L850-UNV-DIM-EMLED	standard
PPXETPZD	FSI8110L830-(UNV347)-DIM-EMLED	standard
P59Z9XMV	FSI8110L830-347-(DIMXDIM)-(_LSXR10 DAYOCC,SWZDT,IAP)	standard
PVK9VVAD	FSI8110L830-UNV-(DIMXDIMSDIM)-(_LSXR10 DAYOCC,SWZDT,IAP)	standard
PJZV7J34	FSI8110L835-(UNV347)-DIM-EMLED	standard
P2W3DZJV	FSI8110L835-347-(DIMXDIM)-(_LSXR10 DAYOCC,SWZDT,IAP)	standard
PRTKZ3AR	FSI8110L835-UNV-(DIMXDIMSDIM)-(_LSXR10 DAYOCC,SWZDT,IAP)	standard
P3Y53AXC	FSI8110L840-(UNV347)-DIM-EMLED	standard
PY1ZENAE	FSI8110L840-347-(DIMXDIM)-(_LSXR10 DAYOCC,SWZDT,IAP)	standard
P8HNNYDC	FSI8110L840-UNV-(DIMXDIMSDIM)-(_LSXR10 DAYOCC,SWZDT,IAP)	standard
PK8MD7PD	FSI8110L850-(UNV347)-DIM-EMLED	standard
P8UVE6KT	FSI8110L850-347-(DIMXDIM)-(_LSXR10 DAYOCC,SWZDT,IAP)	standard
PN758C9E	FSI8110L850-UNV-(DIMXDIMSDIM)-(_LSXR10 DAYOCC,SWZDT,IAP)	standard
PAZEJF2V	FSI8140L830-347-DIM-(_LSXR10 DAYOCC,SWZDT,IAP)	standard
P5C8MHRR	FSI8140L830-UNV-DIM-(_LSXR10 DAYOCC,SWZDT,IAP)	standard
PMSQWD81	FSI8140L830-UNV-DIM-EMLED	standard
P1UZCJ8T	FSI8140L835-347-DIM-(_LSXR10 DAYOCC,SWZDT,IAP)	standard
PFD9S1WT	FSI8140L835-UNV-DIM-(_LSXR10 DAYOCC,SWZDT,IAP)	standard
P46W4UY7	FSI8140L835-UNV-DIM-EMLED	standard
PR6S3RPY	FSI8140L840-347-DIM-(_LSXR10 DAYOCC,SWZDT,IAP)	standard
P4R6ZT79	FSI8140L840-UNV-DIM-(_LSXR10 DAYOCC,SWZDT,IAP)	standard
P895S48K	FSI8140L840-UNV-DIM-EMLED	standard
PV33UJ3N	FSI8140L850-347-DIM-(_LSXR10 DAYOCC,SWZDT,IAP)	standard
PFRF73CS	FSI8140L850-UNV-DIM-(_LSXR10 DAYOCC,SWZDT,IAP)	standard
PYD2GYTJ	FSI8140L850-UNV-DIM-EMLED	standard
P84AFPQ7	FSI860L830-347-DIM-(_LSXR10, DAYOCC,SWZDT,IAP)	standard
PCQ7CG7G	FSI860L830-347-DIM-(_LSXR10, DAYOCC,SWZDT,IAP)	standard
P4A67V2Z	FSI860L830-UNV-DIM-(_LSXR10, DAYOCC,SWZDT,IAP)	standard
PE05XP0R	FSI860L830-UNV-DIM-(_LSXR10, DAYOCC,SWZDT,IAP)	standard
PMHS6303	FSI860L835-347-DIM-(_LSXR10, DAYOCC,SWZDT,IAP)	standard
PBE689GU	FSI860L835-347-DIM-(_LSXR10, DAYOCC,SWZDT,IAP)	standard
PUE76WSE	FSI860L835-UNV-DIM-(_LSXR10, DAYOCC,SWZDT,IAP)	standard
P53N27TM	FSI860L835-UNV-DIM-(_LSXR10, DAYOCC,SWZDT,IAP)	standard
P7RFILJC	FSI860L840-347-DIM-(_LSXR10, DAYOCC,SWZDT,IAP)	standard
PXILVP2M	FSI860L840-347-DIM-(_LSXR10, DAYOCC,SWZDT,IAP)	standard
PZGD575L	FSI860L840-UNV-DIM-(_LSXR10, DAYOCC,SWZDT,IAP)	standard
PFI884HY	FSI860L840-UNV-DIM-(_LSXR10, DAYOCC,SWZDT,IAP)	standard
PJO41L6R	FSI860L850-347-DIM-(_LSXR10, DAYOCC,SWZDT,IAP)	standard
PUAZO2KQ	FSI860L850-347-DIM-(_LSXR10, DAYOCC,SWZDT,IAP)	standard

11/6/2019

Information as of this date. Please check the DLC QPL for confirmation (www.designlights.org/QPL).

Product Id	Model No.	Classification
PALMBJI1	FSI860L850-UNV-DIM-(_LSXR10, DAYOCC, SWZDT, IAP)	standard
P5KL0RZY	FSI860L850-UNV-DIM-(_LSXR10, DAYOCC, SWZDT, IAP)	standard
PU32QDVY	FSI880L830-347-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PU83RYAN	FSI880L830-347-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PJET36MM	FSI880L830-UNV-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PRHFHTG2	FSI880L830-UNV-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PZ17ER42	FSI880L830-UNV-DIM-EMLED	standard
PNMCCYN3	FSI880L830-UNV-DIM-EMLED	standard
PC4JX16Z	FSI880L835-(UNV347)-DIM-EMLED	standard
PVQ4CVDU	FSI880L835-(UNV347)-DIM-EMLED	standard
P4Q1G8T4	FSI880L835-347-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PJP34FP7	FSI880L835-347-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
P4PNXWRH	FSI880L835-UNV-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
P3HZK8D7	FSI880L835-UNV-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PB8SZWP1	FSI880L840-(UNV347)-DIM-EMLED	standard
P892WJN1	FSI880L840-(UNV347)-DIM-EMLED	standard
PPQYGHY	FSI880L840-347-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
P8XQX8Q1	FSI880L840-347-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PDN2ZJ6R	FSI880L840-UNV-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PMDMKR5A	FSI880L840-UNV-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PSM6HUCE	FSI880L850-(UNV347)-DIM-EMLED	standard
PY77MAAY	FSI880L850-(UNV347)-DIM-EMLED	standard
PEVZFSK7	FSI880L850-347-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
P8DTAX2P	FSI880L850-347-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
P3PRWZ3Z	FSI880L850-UNV-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard
PZ8NKAYW	FSI880L850-UNV-(DIMXDIM)-(_LSXR10 DAYOCC, SWZDT, IAP)	standard