

PHILIPS

Bulb

LED

9W - 4W - 2W (60W)

E26

046677464899



One bulb. Your switch. Three color settings.

With the Philips SceneSwitch LED bulb, you can easily change the setting from an inviting ambiance of warm bright light, to a cool and energizing light for more focused tasks. All you need is your existing switch.

High quality light

- Designed for the comfort of your eyes

Light beyond illumination

- No dimmer or additional installation needed
- The lamp can memorize your last setting
- Light color changes at the flick of the existing wall switch

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Auto memory (sceneswitch)



This Scene Switch lamp has a built-in memory chip which will memorize your last light setting if the switch is turned off for longer than 6 seconds. If you don't often switch between activities, the light will be in your favorite mode when you turn it on again.

Plug and play



Delivers a variety of great light scenes straight out of the box to suit your different needs and moods. The intelligence is in the bulb itself, so no dimmer or other additional installation is required. Simply replace your bulb with this Scene Switch bulb, and you can change between different scenes at a flick of your existing wall switch. Lowest level of investment and effort required to enjoy the highest level of comfort. Now you can change the ambience easily to suit whatever you're doing and your mood at the time.

Three light Settings (SSWG)

Flick the switch to change the ambience from soft white, to a warm, cozy light that helps you relax and enjoy the moment. Now you can easily customize your room for a variety of activities or adapt it to suit your mood.

Specifications

Characteristics

- Shape: Bulb
- Dimmable: No
- Socket: E26

Bulb dimensions

- Height: 11.1 cm
- Width: 6.1 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 100,000

Light characteristics

- Beam angle: 300 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 2700-2500-2200 K
- Light Color Category: Warm/Very Warm/Extra Warm
- Nominal luminous flux: 800-320-80 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 135 mA

Power consumption

- Power factor: 0.6
- Voltage: 120 V
- Wattage: 9, 4, 2 W
- Wattage equivalent: 60 W

Rated values

- Rated beam angle: 300 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 800-320-80 lumen
- Rated power: 9-4-2 W

Packaging dimensions and weight

- EAN/UPC – product: 046677464899
- Net weight: 0.130 kg
- Gross weight: 0.160 kg
- Height: 20.400 cm
- Length: 14.400 cm
- Width: 6.400 cm
- Material number (12NC): 929001261305



Issue date: 2023-11-07
Version: 0.522

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com