

PHILIPS

Reflector
(Dimmable)

LED

13W-120W

E26

Bright White Light

Dimming



046677532505



Dimmable LED light with a focused bright beam

Philips dimmable LED PAR spot light bulbs are a long lasting, energy efficient replacement for halogen spots. They have a bright white light and are ideal for general and flood lighting.

High quality light

- Designed for the comfort of your eyes

Light beyond illumination

- Dimmable
- Instant on

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Instant on

Dimmable

This bulb can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this bulb.

Specifications

Bulb characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: E26
- Technology: LED

Bulb dimensions

- Height: 12.9 cm
- Weight: 0.374 kg
- Width: 12.2 cm

Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 25,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 40 degree(s)
- Color consistency: 4SDCM
- Color rendering index (CRI): 90
- Color temperature: 3000 K
- Light Color Category: Bright White
- Nominal luminous flux: 1200 lumen
- Starting time: 0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 120 mA
- Efficacy: 92 lm/W

Packaging information

- EAN: 046677532505
- EOC: 532507
- Product title: 13PAR38/LED/930/F40/DIM/GULW T20 2/2FB

Power consumption

- Power factor: 0.8
- Voltage: 120 V
- Wattage: 13 W
- Wattage equivalent: 120 W

Product dimensions & weight

- Length: 12.9 cm

Rated values

- Rated beam angle: 40 degree(s)
- Rated lifetime: 25,000 hour(s)
- Rated peak intensity: 2231 cd
- Rated power: 13 W

Technical specifications

- Frequency: 50-60 Hz

Bulb characteristics

- EAN/UPC - product: 046677532505
- Rated beam angle: 40 degree(s)
- Height: 12.9 cm
- Average life (at 2.7 hrs/day): 25 year(s)
- Beam angle: 40 degree(s)
- Lamp current: 120 mA
- Net weight: 0.772 kg
- Rated lifetime: 25,000 hour(s)
- Intended use: Indoor
- Weight: 0.374 kg
- Lumen maintenance factor: 70%
- Color consistency: 4SDCM
- Gross weight: 0.840 kg
- EAN: 046677532505
- Lamp shape: Directional reflector
- Width: 12.2 cm
- Color rendering index (CRI): 90
- Height: 11.500 cm
- EOC: 532507
- Rated peak intensity: 2231 cd
- Socket: E26
- Number of switch cycles: 50,000
- Color temperature: 3000 K
- EyeComfort: Yes
- Length: 11.300 cm
- Product title: 13PAR38/LED/930/F40/DIM/GULW T20 2/2FB
- Power factor: 0.8
- Rated power: 13 W
- Technology: LED
- Light Color Category: Bright White
- Width: 21.500 cm
- Voltage: 120 V
- Nominal luminous flux: 1200 lumen
- Material number (12NC): 929001949326
- Wattage: 13 W
- Length: 12.9 cm
- Starting time: 0.5 s
- Wattage equivalent: 120 W
- Warm-up time to 60% light: Instant full light
- Frequency: 50-60 Hz



Issue date: 2022-06-12
Version: 0.201

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com