

PHILIPS

Linear tube

LED

30W-60W

FA8

Daylight

046677542498



LED tube that works directly from your power line

Philips MainsFit LED tubes replace fluorescent tubes by operating directly from the power line and any existing socket. This 8-foot glass LED tube looks and feels similar to fluorescent and provides a daylight effect with long lifetime.

Specifications

Characteristics

- Dimmable: Non Dimmable
- Intended use: Indoor
- Lamp shape: Linear tube
- Socket: FA8
- Lamp shape code: T8
- Control: On/off switch

Durability

- Nominal lifetime: 36,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Application: Task lighting
- Color rendering index (CRI): 80
- Nominal luminous flux: 3500 lumen

Other characteristics

- Lamp current: 120–275 mA
- Efficacy: 116 lm/W

Packaging information

- Product family: MainsFit

Power consumption

- Power factor: 0.9

Product dimensions & weight

- Length: 240 cm

Rated values

- Rated beam angle: 240 degree(s)
- Rated power: 30 W

Technical specifications

- Frequency: 50–60 Hz

Packaging dimensions and weight

- EAN/UPC – product: 046677542498
- Net weight: 1.080 kg
- Gross weight: 1.240 kg
- Height: 240.000 cm
- Length: 5.800 cm
- Width: 5.800 cm
- Material number (12NC): 929001919503



Issue date: 2023-11-08
Version: 0.192

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com