

# PHILIPS

Bulb

LED

26W-125W

E26

Daylight Deluxe

046677545130



## Bright LED lighting with excellent light quality

Philips LED light bulbs provide a cool white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your matted traditional bulbs.

### High quality light

- Long life bulb - Lasts up to 10 years

### Choose for a sustainable solution

- Saves up to 80% Energy

### Light beyond illumination

- A simple LED for everyday use

# Highlights

## 10,950-hour rated average life

With a lifetime of up to 10,950 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 10 years.

## Saves up to 80% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

## A simple LED for everyday use



The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from LED at an affordable price.

# Specifications

## Characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Other
- Socket: E26
- Technology: LED
- Type of glass: Frosted

## Bulb dimensions

- Height: 7.7 cm
- Weight: 0.248 kg
- Width: 20 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 120 degree(s)
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Light Color Category: Daylight Deluxe
- Nominal luminous flux: 2050 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 360 mA
- Efficacy: 78 lm/W

## Packaging information

- EAN: 046677545130
- EOC: 545137
- Product title: 26UFO/LED/865/FR/P/ND 6/1FB

#### Power consumption

- Power factor: 0.5
- Voltage: 110-240 V
- Wattage: 26 W
- Wattage equivalent: 125 W

#### Product dimensions & weight

- Length: 7.7 cm

#### Rated values

- Rated beam angle: 120 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 2050 lumen
- Rated power: 26 W

#### Technical specifications

- Frequency: 50-60 Hz

#### Packaging dimensions and weight

- EAN/UPC - product: 046677545130
- Net weight: 0.253 kg
- Gross weight: 0.265 kg
- Height: 21.000 cm
- Length: 21.000 cm
- Width: 8.500 cm
- Material number (12NC):  
929002010805



Issue date: 2021-01-11  
Version: 0.18

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)