

PHILIPS

Linear tube

LED

16-25-28-30-32W

G13

Daylight Deluxe

046677545611



Simple T8 LED replacement for fluorescent tubes

Philips InstantFit LED tubes easily replace fluorescent T8 tubes operated on instant-start electronic ballasts, no rewiring needed. This glass LED linear bulb looks and feels like fluorescent with a daylight deluxe effect and long lifetime.

High quality light

- Cool, day light

Choose for a sustainable solution

- You can trust what the Philips packaging is saying.

Light beyond illumination

- Instant on

Highlights

Cool, day light



This bulb has a color temperature of 6500K, and is the highest color temperature available in this bulb category. It therefore gives you a lighting effect that is the closest to that of natural daylight. This will help you focus and experience every detail.

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

Instant on

Specifications

Characteristics

- Dimmable: Non Dimmable
- Intended use: Indoor
- Lamp shape: Linear tube
- Socket: G13
- Technology: LED
- Lamp shape code: T8
- Control: On/off switch

Bulb dimensions

- Height: 121.23 cm
- Weight: 0.22 kg
- Width: 2.78 cm

Durability

- Average life (at 2.7 hrs/day): 37 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 36,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Application: Task lighting
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Light Color Category: Daylight Deluxe
- Nominal luminous flux: 1800 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 110-330 mA
- Efficacy: 112 lm/W

Packaging information

- Product family: UniversalFit
- EAN: 046677545611
- Product title: 16T8/LED/48-865/IF18/G 10/1 FB

Power consumption

- Power factor: >0.9
- Voltage: 120-277, 347 V
- Wattage: 16 W
- Wattage equivalent: 25-28-30-32 W

Product dimensions & weight

- Length: 121.23 cm

Rated values

- Rated beam angle: 240 degree(s)
- Rated lifetime: 36,000 hour(s)
- Rated luminous flux: 1800 lumen
- Rated power: 16 W

Technical specifications

- Frequency: 20-120 Hz

Packaging dimensions and weight

- EAN/UPC - product: 046677545611
- Net weight: 0.440 kg
- Gross weight: 0.580 kg
- Height: 123.300 cm
- Length: 3.000 cm
- Width: 3.000 cm
- Material number (12NC): 929001961033



Issue date: 2021-06-04
Version: 0.260

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com