

# PHILIPS

Bulb (Dimmable)

LED

8.8W-60W

E26

2200-2700

Dimming

046677548391



## The right light makes the moment

Philips LEDs with a dimmable warm glow effect, enables light levels to dim to the warm tones of traditional bulbs. You can change the ambience from functional lighting to an inviting and cozy atmosphere.

### Choose a simple replacement for your old bulbs

- Similar shape and size as standard incandescent bulb

### Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years
- Saves up to 80% Energy
- Title 20 for Sale in California

### Light beyond illumination

- Dims to a warm glow
- Dimmable

### High quality LED light that lasts for decades

- Designed for the comfort of your eyes

# Highlights

## Replaces standard incandescent

With its beautiful design and familiar shape, this energy-saving LED bulb is the perfect sustainable replacement for traditional incandescent bulbs.

## 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

## Saves up to 80% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

## Title 20

This bulb has been designed in compliance with CEC regulations for California Title 20, for sale in California.

## Dims to a warm glow

With this dimmable bulb, you can dim from a 2200k warm light to a 2700K light. The more you dim, the warmer the light..

## Dimmable

This bulb can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this bulb.

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Specifications

## Bulb characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E26
- Technology: LED
- Type of glass: Frosted

## Bulb dimensions

- Height: 11.15 cm
- Weight: 0.06 kg
- Width: 6.25 cm

**Durability**

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

**Light characteristics**

- Beam angle: 250 degree(s)
- Color consistency: 4SDCM
- Color rendering index (CRI): 90
- Color temperature: 2200-2700 K
- Light Color Category: Soft White Warm Glow Effect
- Nominal luminous flux: 800 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

**Miscellaneous**

- EyeComfort: Yes

**Other characteristics**

- Lamp current: 80 mA
- Efficacy: 90 lm/W

**Packaging information**

- EAN: 046677548391
- EOC: 548396
- Product title: 8.8A19/PER/927-22/P/E26/WG4/4BB T20

**Power consumption**

- Energy Star Certified: Yes
- Power factor: >0.7
- Voltage: 120 V
- Wattage: 8.8 W
- Wattage equivalent: 60 W

**Product dimensions & weight**

- Length: 11.15 cm

**Rated values**

- Rated beam angle: 250 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 800 lumen
- Rated power: 8.8 W

**Technical specifications**

- Frequency: 60 Hz

**Bulb characteristics**

- EAN/UPC - product: 046677548391
- Rated beam angle: 250 degree(s)
- Height: 11.15 cm
- Average life (at 2.7 hrs/day): 15 year(s)
- Beam angle: 250 degree(s)
- Lamp current: 80 mA
- Net weight: 0.200 kg
- Rated lifetime: 15,000 hour(s)
- Intended use: Indoor
- Weight: 0.06 kg
- Lumen maintenance factor: 70%
- Color consistency: 4SDCM
- Gross weight: 0.286 kg
- EAN: 046677548391
- Energy Star Certified: Yes
- Rated luminous flux: 800 lumen
- Lamp shape: Non directional bulb
- Width: 6.25 cm
- Color rendering index (CRI): 90
- Height: 17.000 cm
- EOC: 548396
- Socket: E26
- Number of switch cycles: 50,000
- Color temperature: 2200-2700 K
- EyeComfort: Yes
- Length: 6.500 cm
- Product title: 8.8A19/PER/927-22/P/E26/WG4/4BB T20
- Power factor: >0.7
- Rated power: 8.8 W
- Technology: LED
- Light Color Category: Soft White Warm Glow Effect
- Width: 19.700 cm
- Voltage: 120 V
- Type of glass: Frosted
- Nominal luminous flux: 800 lumen
- Material number (12NC): 929001940993
- Wattage: 8.8 W
- Length: 11.15 cm
- Starting time: <0.5 s
- Wattage equivalent: 60 W
- Warm-up time to 60% light: Instant full light
- Frequency: 60 Hz



Issue date: 2022-06-12  
Version: 0.18

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)