

# PHILIPS

Candle (Dimmable)

LED

5.5W-60W

E26

Daylight

Dimming

046677549428



## The right light makes the moment

Familiar shapes you know and love. They use around 80% less energy than traditional light bulbs and last ten times longer.

### Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years
- Saves up to 80% Energy

# Highlights

## 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of

frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

## Saves up to 80% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

# Specifications

## Characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: B11
- Socket: E26
- Technology: LED
- Type of glass: Clear

## Bulb dimensions

- Height: 9.2 cm
- Weight: 0.02 kg
- Width: 3.5 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

## Light characteristics

- Color consistency: 4SDCM
- Color rendering index (CRI): 90
- Color temperature: 5000 K
- Light Color Category: Daylight
- Nominal luminous flux: 500 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 60 mA
- Efficacy: 90 lm/W

## Packaging information

- EAN: 046677549428
- EOC: 549428
- Product title:  
5.5B11/PER/950/CL/G/E26/DIM  
1FBT20

## Power consumption

- Power factor: 0.7
- Voltage: 120 V
- Wattage: 5.5 W
- Wattage equivalent: 60 W

## Product dimensions & weight

- Length: 9.2 cm

## Rated values

- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 500 lumen
- Rated power: 5.5 W

## Technical specifications

- Frequency: 60 Hz

**Packaging dimensions and weight**

- EAN/UPC - product: 046677549428
- Net weight: 0.016 kg
- Gross weight: 0.032 kg
- Height: 11.000 cm
- Length: 4.500 cm
- Width: 4.500 cm
- Material number (12NC): 929002206404



Issue date: 2023-11-08  
Version: 0.196

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)