

# PHILIPS

Bulb (Dimmable)

LED

8.8W-60W

E26

Soft White Light Warm Glow  
Effect

Dimming

046677554408



## Light that's easy on your eyes

Poor quality light could cause eye strain. It's more important than ever to properly light your home. Philips LED lamps fulfill stringent test criteria to ensure they meet our Eyecomfort requirements†

# Specifications

## Bulb characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E26

## Bulb dimensions

- Height: 11.15 cm
- Width: 6.25 cm

## Durability

- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 250 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 2200–2700 K
- Nominal luminous flux: 800 lm
- Warm-up time to 60% light: instant full light

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Efficacy: 90 lm/W

## Packaging information

- EAN: 046677554408
- EOC: 554402
- Product title: 8.8A19/PER/927-22/P/E26/WG 6/1FB T20

## Power consumption

- Energy Star Certified: Yes
- Power factor: >0.7
- Voltage: 120 V
- Wattage: 8.8 W
- Wattage equivalent: 60 W



Issue date: 2024-02-02  
Version: 0.204

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)