

PHILIPS

Bulb

LED

8.8W-60W

E26

Daylight

046677554613



Bright LED lighting with excellent light quality

Familiar shapes you know and love. They use around 80% less energy than traditional light bulbs and last ten times longer.

High quality light

- Long life bulb - Lasts up to 10 years

Choose a simple replacement for your old bulbs

- Similar shape and size as standard incandescent bulb

Choose for a sustainable solution

- Title 20 for Sale in California

High quality LED light that lasts for decades

- Designed for the comfort of your eyes
- Light that shows true colors

Highlights

10,950-hour rated average life

With a lifetime of up to 10,950 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 10 years.

Replaces standard incandescent

With its beautiful design and familiar shape, this energy-saving LED bulb is the perfect sustainable replacement for traditional incandescent bulbs.

Title 20

This bulb has been designed in compliance with CEC regulations for California Title 20, for sale in California.

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Light that shows true colors



See the true colors of your clothes when you select an outfit from your wardrobe – you can pair a red dress and red shoes with confidence and be sure the colors match perfectly.

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E26
- Technology: LED
- Type of glass: Frosted

Bulb dimensions

- Height: 11.2 cm
- Weight: 0.035 kg
- Width: 6.1 cm

Durability

- Average life (at 2.7 hrs/day): 11 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 11,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 210 degree(s)
- Color consistency: 4SDCM
- Color rendering index (CRI): 90
- Color temperature: 5000 K
- Light Color Category: Daylight
- Nominal luminous flux: 800 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 105 mA
- Efficacy: 90 lm/W

Packaging information

- EAN: 046677554613
- EOC: 554618
- Product title: 8.8A19/LED/950/P/E26/ND 4/4FB T20

Power consumption

- Power factor: >0.7
- Voltage: 120 V
- Wattage: 8.8 W
- Wattage equivalent: 60 W

Rated values

- Rated beam angle: 210 degree(s)
- Rated lifetime: 11,000 hour(s)
- Rated luminous flux: 800 lumen
- Rated power: 8.8 W

Packaging dimensions and weight
[8.8A19/LED/950/FR/P/E26/ND/T20
4/4FB]

- EAN/UPC – product: 046677554613
- Net weight: 0.135 kg
- Gross weight: 0.188 kg
- Height: 17.600 cm
- Length: 6.200 cm
- Width: 12.200 cm
- Material number (12NC):
929003020403

Packaging dimensions and weight
[8.8A19/LED/950/P/E26/ND 4/4FB
T20]

- EAN/UPC – product: 046677554613
- Net weight: 0.136 kg
- Gross weight: 0.188 kg
- Height: 17.600 cm
- Length: 6.200 cm
- Width: 12.200 cm
- Material number (12NC):
929002227303



Issue date: 2023-11-08
Version: 0.329

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com