

PHILIPS

Bulb (Dimmable)

LED

7.2W-65W

E26

Daylight

Dimming

046677555894



Bright LED lighting with excellent light quality

Familiar shapes you know and love. They use around 80% less energy than traditional light bulbs and last ten times longer.

High quality light

- Natural day light

Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years
- Saves up to 80% Energy

Light beyond illumination

- Dimmable

High quality LED light that lasts for decades

- Designed for the comfort of your eyes

Highlights

Natural day light



This bulb has a color temperature of 5000K, creating a lighting effect that is very close to that of natural daylight. Natural daylight helps with focus and making details easier to see.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Saves up to 80% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

Dimmable

This bulb can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this bulb.

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Non directional reflector
- Socket: E26
- Technology: LED
- Type of glass: Frosted

Bulb dimensions

- Height: 13.2 cm
- Weight: 0.09 kg
- Width: 9.5 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 90 degree(s)
- Color consistency: 4SDCM
- Color rendering index (CRI): 90
- Color temperature: 5000 K
- Light Color Category: Daylight
- Nominal luminous flux: 650 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 82 mA
- Efficacy: 90 lm/W

Packaging information

- EAN: 046677555894
- EOC: 555896
- Product title:
7.2BR30/PER/950/P/E26/DIM 4/2FB
T20

Power consumption

- Power factor: >0.7
- Voltage: 120 V
- Wattage: 7.2 W
- Wattage equivalent: 65 W

Product dimensions & weight

- Length: 13.2 cm

Rated values

- Rated beam angle: 90 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 650 lumen
- Rated power: 7.2 W

Technical specifications

- Frequency: 60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 046677555894
- Net weight: 0.188 kg
- Gross weight: 0.248 kg
- Height: 14.500 cm
- Length: 9.100 cm
- Width: 13.900 cm
- Material number (12NC):
929002204135



Issue date: 2021-01-11
Version: 0.15

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com