

PHILIPS

Reflector
(Dimmable)

LED

8.5W-75W

E26

Daylight

Dimming

046677556693



Dimmable LED light with a focused bright beam

Philips dimmable LED PAR spot light bulbs are a long lasting, energy efficient replacement for halogen spots. They have a bright white light and are ideal for general and flood lighting.

High quality light

- Designed for the comfort of your eyes

Choose a simple replacement for your old bulbs

- Ideal LED replacement: incandescent/halogen globe
- Suitable for enclosed fixtures

Choose for a sustainable solution

- Long life bulbs - Lasts up to 25 years

Create the right light for your home

- Perfect for accent lighting

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Replaces globe

This is an energy-saving standard LED bulb designed to match the look and dimensions of traditional light bulbs. The perfect sustainable replacement for standard incandescent & halogen globe bulbs - longer lasting and much more energy efficient.

Suitable for enclosed fixtures

This LED bulb can be used in enclosed fixtures.

25,000-hour rated average life



With a lifetime of up to 25,000 hours, you can reduce the hassle of frequently replacing your light bulbs and enjoy a perfect lighting solution for over 25 years.

40° deg beam - flood [LED lamps]

An LED flood with a wide-angle light output (40 degrees), suitable for both accent lighting and general purpose lighting.

Specifications

Bulb characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: E26
- Technology: LED

Bulb dimensions

- Height: 11.6 cm
- Weight: 0.24 kg
- Width: 9.4 cm

Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 25,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 40 degree(s)
- Color consistency: 4SDCM
- Color rendering index (CRI): 90
- Color temperature: 5000 K
- Light Color Category: Daylight
- Nominal luminous flux: 850 lumen
- Starting time: 0.5 s
- Warm-up time to 60% light: instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 80 mA
- Efficacy: 100 lm/W

Packaging information

- EAN: 046677556693
- EOC: 556696
- Product title:
8.5PAR30L/LED/950/F40/DIM/G
T20 4/1FB

Power consumption

- Power factor: 0.8
- Voltage: 120 V
- Wattage: 8.5 W
- Wattage equivalent: 75 W

Product dimensions & weight

- Length: 11.6 cm

Rated values

- Rated beam angle: 40 degree(s)
- Rated lifetime: 25,000 hour(s)
- Rated peak intensity: 1315 cd
- Rated power: 8.5 W

Technical specifications

- Frequency: 50-60 Hz



Issue date: 2023-11-08
Version: 0.79

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com