

# PHILIPS

Bulb (Dimmable)

LED

10W-60W

E26

Soft White

Dimming

046677556761



## Soft white light, no compromise on light quality

Philips LED lusters provide a beautiful, soft white light, an exceptionally long life and immediate, significant energy savings. With a pure and elegant design, this light bulb is the perfect replacement for your incandescent lusters..

### High quality light

- Long life bulb - Lasts up to 10 years

### Light beyond illumination

- A simple LED for everyday use
- Instant on

### High quality LED light that lasts for decades

- Designed for the comfort of your eyes

# Highlights

## 10,950-hour rated average life

With a lifetime of up to 10,950 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 10 years.

## A simple LED for everyday use



The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from LED at an affordable price.

## Instant on

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Specifications

## Bulb characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E26
- Technology: LED
- Type of glass: Frosted

## Bulb dimensions

- Height: 10.2 cm
- Weight: 0.034 kg
- Width: 6 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

## Light characteristics

- Beam angle: 240 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Light Color Category: Soft White
- Nominal luminous flux: 800 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

## Miscellaneous

- EyeComfort: No

## Other characteristics

- Lamp current: 110 mA
- Efficacy: 80 lm/W

## Packaging information

- EAN: 046677556761
- EOC: 556761
- Product title: 10A19/PER/827/P/E26/DIM 24/4FB

#### Power consumption

- Power factor: >0.6
- Voltage: 120 V
- Wattage: 10 W
- Wattage equivalent: 60 W

#### Rated values

- Rated beam angle: 240 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 800 lumen
- Rated power: 10 W

#### Packaging dimensions and weight

- EAN/UPC - product: 046677556761
- Net weight: 0.220 kg
- Gross weight: 0.268 kg
- Height: 17.500 cm
- Length: 6.100 cm
- Width: 12.100 cm
- Material number (12NC):  
929002260505



Issue date: 2020-08-03  
Version: 0.13

© 2020 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.