

# PHILIPS

Bulb (Dimmable)

LED

10W-60W

E26

Daylight

Dimming

046677556778



## Bright LED lighting with excellent light quality

Philips LED light bulbs provide a cool white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your matted traditional bulbs.

### High quality light

- Long life bulb - Lasts up to 10 years

### Light beyond illumination

- A simple LED for everyday use
- Instant on

### High quality LED light that lasts for decades

- Designed for the comfort of your eyes

# Highlights

## 10,950-hour rated average life

With a lifetime of up to 10,950 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 10 years.

## A simple LED for everyday use



The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from LED at an affordable price.

## Instant on

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Specifications

## Bulb characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E26
- Technology: LED
- Type of glass: Frosted

## Bulb dimensions

- Height: 10.2 cm
- Weight: 0.034 kg
- Width: 6 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

## Light characteristics

- Beam angle: 240 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 5000 K
- Light Color Category: Daylight
- Nominal luminous flux: 800 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

## Miscellaneous

- EyeComfort: No

## Other characteristics

- Lamp current: 110 mA
- Efficacy: 80 lm/W

## Packaging information

- EAN: 046677556778
- EOC: 556779
- Product title: 10A19/PER/850/P/E26/DIM 24/4FB

**Power consumption**

- Power factor: >0.6
- Voltage: 120 V
- Wattage: 10 W
- Wattage equivalent: 60 W

**Product dimensions & weight**

- Length: 10.2 cm

**Rated values**

- Rated beam angle: 240 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 800 lumen
- Rated power: 10 W

**Technical specifications**

- Frequency: 60 Hz

**Bulb characteristics**

- EAN/UPC – product: 046677556778
- Rated beam angle: 240 degree(s)
- Height: 10.2 cm
- Average life (at 2.7 hrs/day): 15 year(s)
- Beam angle: 240 degree(s)
- Lamp current: 110 mA
- Net weight: 0.220 kg
- Rated lifetime: 15,000 hour(s)
- Intended use: Indoor
- Weight: 0.034 kg
- Lumen maintenance factor: 70%
- Color consistency: 6SDCM
- Gross weight: 0.268 kg
- EAN: 046677556778
- Rated luminous flux: 800 lumen
- Lamp shape: Non directional bulb
- Width: 6 cm
- Color rendering index (CRI): 80
- Height: 17.500 cm
- EOC: 556779
- Socket: E26
- Number of switch cycles: 20,000
- Color temperature: 5000 K
- EyeComfort: No
- Length: 6.100 cm
- Product title:  
10A19/PER/850/P/E26/DIM 24/4FB
- Power factor: >0.6
- Rated power: 10 W
- Technology: LED
- Light Color Category: Daylight
- Width: 12.100 cm
- Voltage: 120 V
- Type of glass: Frosted
- Nominal luminous flux: 800 lumen
- Material number (12NC):  
929002260605
- Wattage: 10 W
- Length: 10.2 cm
- Starting time: <0.5 s
- Wattage equivalent: 60 W
- Warm-up time to 60% light: Instant full light
- Frequency: 60 Hz



Issue date: 2023-11-07  
Version: 0.19

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)