

PHILIPS

Bulb

LED

14-8-5W-100-60-40W

E26

Soft White

046677556921



State-of-the-art LED light bulb for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E26
- Technology: LED
- Type of glass: Frosted
- Bulb Finish: Frosted

Bulb dimensions

- Height: 13.31 cm
- Weight: 0.094 kg
- Width: 7.06 cm

Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 25,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 250 degree(s)
- Color consistency: 4SDCM
- Color rendering index (CRI): 90
- Color temperature: 2700 K
- Light Color Category: Soft White
- Nominal luminous flux: 1600-800-450 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: 0.5 s
- Color Code: 927 | CCT of 2700K
- Correlated Color Temperature (Nom): 2700 K
- Luminous Efficacy (rated) (Nom): 114.00 lm/W

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 120-56-38 mA
- Efficacy: 114 lm/W
- EU RoHS compliant: Yes

Packaging dimensions and weight

- Net weight: 0.096 kg

Packaging information

- EAN: 046677556921
- EOC: 556928
- Product title: 14A21/LED/927/P/E26/3WAY ND 4/1FB T20

Power

- Power Factor (Fraction): 0.7

Power consumption

- Power factor: 0.7
- Voltage: 120 V
- Wattage: 14, 8, 5 W
- Wattage equivalent: 100-60-40 W
- Power Consumption: 14, 5, 8 W

Product dimensions & weight

- Length: 13.31 cm

Rated values

- Rated beam angle: 250 degree(s)
- Rated lifetime: 25,000 hour(s)
- Rated luminous flux: 1600-800-450 lumen
- Rated power: 14-8-5 W

Technical specifications

- Frequency: 60 Hz
- Dimmable: No
- Line Frequency: 60 Hz
- Cap-Base: E26 | Single Contact Medium Screw

Packaging dimensions and weight

- EAN/UPC - product: 046677556921
- Gross weight: 0.114 g
- Height: 14.000
- Length: 7.500
- Width: 7.500
- Material number (12NC): 929002285003



Issue date: 2023-11-08
Version: 0.17

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com