

**PHILIPS**

Bulb

LED

14-8-5W-100-60-40W

E26

Soft White

046677556945



## State-of-the-art LED light bulb for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E26
- Technology: LED
- Type of glass: Frosted

## Bulb dimensions

- Height: 13.31 cm
- Weight: 0.094 kg
- Width: 7.06 cm

## Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 25,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 250 degree(s)
- Color consistency: 4SDCM
- Color rendering index (CRI): 90
- Color temperature: 2700 K
- Light Color Category: Soft White
- Nominal luminous flux: 1600-800-450 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 927 | CCT of 2700K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 120-56-38 mA
- Efficacy: 114 lm/W

## Packaging information

- EAN: 046677556945
- EOC: 556944
- Product title: 14A21/LED/927/P/E26/3WAY ND 4/1FB T20

## Power consumption

- Energy Star Certified: Yes
- Power factor: 0.7
- Voltage: 120 V
- Wattage: 14, 8, 5 W
- Wattage equivalent: 100-60-40 W

## Product dimensions & weight

- Length: 13.31 cm

## Rated values

- Rated beam angle: 250 degree(s)
- Rated lifetime: 25,000 hour(s)
- Rated luminous flux: 1600-800-450 lumen
- Rated power: 14-8-5 W

## Technical specifications

- Frequency: 60 Hz

**Bulb characteristics**

- EAN/UPC - product: 046677556945
- Rated beam angle: 250 degree(s)
- Height: 13.31 cm
- Average life (at 2.7 hrs/day): 25 year(s)
- Beam angle: 250 degree(s)
- Lamp current: 120-56-38 mA
- Net weight: 0.096 kg
- Rated lifetime: 25,000 hour(s)
- Intended use: Indoor
- Weight: 0.094 kg
- Lumen maintenance factor: 70%
- Color consistency: 4SDCM
- Gross weight: 0.114 kg
- EAN: 046677556945
- Energy Star Certified: Yes
- Rated luminous flux: 1600-800-450 lumen
- Lamp shape: Non directional bulb
- Width: 7.06 cm
- Color rendering index (CRI): 90
- Height: 14.000 cm
- EOC: 556944
- Socket: E26
- Number of switch cycles: 50,000
- Color temperature: 2700 K
- EyeComfort: Yes
- Length: 7.500 cm
- Product title: 14A21/LED/927/P/E26/3WAY ND 4/1FB T20
- Power factor: 0.7
- Rated power: 14-8-5 W
- Technology: LED
- Light Color Category: Soft White
- Width: 7.500 cm
- Voltage: 120 V
- Type of glass: Frosted
- Nominal luminous flux: 1600-800-450 lumen
- Material number (12NC): 929002285005
- Wattage: 14, 8, 5 W
- Length: 13.31 cm
- Starting time: <0.5 s
- Wattage equivalent: 100-60-40 W
- Warm-up time to 60% light: Instant full light
- Color Code: 927 | CCT of 2700K
- Frequency: 60 Hz



Issue date: 2022-06-12  
Version: 0.21

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)