

PHILIPS

Reflector
(Dimmable)

LED

8.5W-75W

E26

Bright White

Dimming

046677557539



Extra bright, dimmable glass spot

Show your home in its best light with Philips high lumen LED light bulbs. No more dark areas, the brighter light output removes shadows, even from a distance. The extra brightness helps make reading and other activities easier on the eyes.

High quality light

- Designed for the comfort of your eyes
- Bright white light

Choose a simple replacement for your old bulbs

- Similar shape and size as halogen reflector

Light beyond illumination

- Dimmable

Designed to be seen, looks good on and off

- Classic glass LED

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Bright white light



This bulb has a color temperature of 3000K providing you with a bright, warm light, perfect for creating an inviting ambience to host friends or wind down with a book.

Replaces halogen spot



With its beautifully shaped design and familiar dimensions, this is a modern lighting, LED reflector. The perfect sustainable replacement for traditional halogen reflectors.

Dimmable

This bulb can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this bulb.

Glass Clear Design

The look you love, the performance you expect. Classic clear glass designs that replicate the beautiful sparkling light of traditional bulbs, for a perfect fit throughout your home.

Specifications

Bulb characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: E26
- Technology: LED

Bulb dimensions

- Height: 8.4 cm
- Weight: 0.134 kg
- Width: 6.4 cm

Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 25,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 40 degree(s)
- Color consistency: 4SDCM
- Color rendering index (CRI): 90
- Color temperature: 3000 K
- Light Color Category: Bright White
- Nominal luminous flux: 800 lumen
- Starting time: 0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 124 mA
- Efficacy: 94 lm/W

Packaging information

- EAN: 046677557539
- EOC: 557538
- Product title:
8.5PAR20/LED/930/F40/D/G/HO
T20 4/1FB

Power consumption

- Power factor: 0.7
- Voltage: 120 V
- Wattage: 8.5 W
- Wattage equivalent: 75 W

Product dimensions & weight

- Length: 8.4 cm

Rated values

- Rated beam angle: 40 degree(s)
- Rated lifetime: 25,000 hour(s)
- Rated peak intensity: 1270 cd
- Rated power: 8.5 W

Technical specifications

- Frequency: 50-60 Hz

Bulb characteristics

- EAN/UPC - product: 046677557539
- Rated beam angle: 40 degree(s)
- Height: 8.4 cm
- Average life (at 2.7 hrs/day): 25 year(s)
- Beam angle: 40 degree(s)
- Lamp current: 124 mA
- Net weight: 0.135 kg
- Rated lifetime: 25,000 hour(s)
- Intended use: Indoor
- Weight: 0.134 kg
- Lumen maintenance factor: 70%
- Color consistency: 4SDCM
- Gross weight: 0.166 kg
- EAN: 046677557539
- Lamp shape: Directional reflector
- Width: 6.4 cm
- Color rendering index (CRI): 90
- Height: 9.000 cm
- EOC: 557538
- Rated peak intensity: 1270 cd
- Socket: E26
- Number of switch cycles: 50,000
- Color temperature: 3000 K
- EyeComfort: Yes
- Length: 7.000 cm
- Product title:
8.5PAR20/LED/930/F40/D/G/HO
T20 4/1FB
- Power factor: 0.7
- Rated power: 8.5 W
- Technology: LED
- Light Color Category: Bright White
- Width: 7.000 cm
- Voltage: 120 V
- Nominal luminous flux: 800 lumen
- Wattage: 8.5 W
- Length: 8.4 cm
- Starting time: 0.5 s
- Wattage equivalent: 75 W
- Warm-up time to 60% light: Instant full light
- Frequency: 50-60 Hz



Issue date: 2022-05-11
Version: 0.17

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com