

# PHILIPS

Bulb

LED

8.8W-60W

E26

Soft White

046677557737



## Dusk to Dawn

Philips LED Dusk to Dawn bulb is designed to save even more energy than regular LED by turning itself on and off with the level of daylight - providing secure light during the night, and turning off with the light of day.

### High quality light

- True incandescent-like warm white light

### Choose a simple replacement for your old bulbs

- Similar shape and size as standard incandescent bulb

### Choose for a sustainable solution

- Long life bulbs - Lasts up to 25 years
- Saves up to 80% Energy
- Title 20 for Sale in California

### Light beyond illumination

- Built-in automatic on/off light sensor

# Highlights

## Incandescent-like warm white



This bulb has a color temperature of 2700K, providing you with a warm, tranquil atmosphere, perfect for relaxing. This 2700K light is ideal for home lighting design

## Replaces standard incandescent

With its beautiful design and familiar shape, this energy-saving LED bulb is the perfect sustainable replacement for traditional incandescent bulbs.

## 25,000-hour rated average life



With a lifetime of up to 25,000 hours, you can reduce the hassle of frequently replacing your light bulbs and enjoy a perfect lighting solution for over 25 years.

## Saves up to 80% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

## Title 20

This bulb has been designed in compliance with CEC regulations for California Title 20, for sale in California.

## Day and night sensor



With its built-in automatic light sensor, this bulb switches on automatically after dusk and off after dawn.

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E26
- Technology: LED
- Type of glass: Frosted

## Bulb dimensions

- Height: 10.98 cm
- Weight: 0.062 kg
- Width: 6.15 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

**Light characteristics**

- Beam angle: 220 degree(s)
- Color consistency: 4SDCM
- Color rendering index (CRI): 90
- Color temperature: 2700 K
- Light Color Category: Soft White
- Nominal luminous flux: 800 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: instant full light
- Color Code: 927 | CCT of 2700K

**Miscellaneous**

- EyeComfort: Yes

**Other characteristics**

- Lamp current: 74 mA
- Efficacy: 90 lm/W

**Packaging information**

- EAN: 046677557737
- EOC: 557736
- Product title: 8.8A19/AMB/927/ND D2D 4/1FB T20

**Power consumption**

- Power factor: 0.7
- Voltage: 120 V
- Wattage: 8.8 W
- Wattage equivalent: 60 W

**Product dimensions & weight**

- Length: 10.98 cm

**Rated values**

- Rated beam angle: 220 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 800 lumen
- Rated power: 8.8 W

**Technical specifications**

- Frequency: 60 Hz



Issue date: 2023-11-07  
Version: 0.23

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)