


Decorative Anchor Base Post (302-) Specification Sheet

Project Name:	Location:	MFG: Hadco
Fixture Type:	Catalog No.:	Qty:



Ordering Guide

Example: 302- 9 ABS B B

Product Code	302-	Decorative Anchor Base Post
Height(s)	9	(9 ft.)
Finish	ABS ACP ARD ASI BLK BRN BRZ FGN GRA IRN IRN RBZ SRT VBC VGN VTC WBZ WHT	Antique Brass Antique Copper Antique Red Antique Silver Black Brown Bronze Forest Green Granite Ironstone Rustic Bronze Shadow Rust Verde Bronze Verde Copper Verde Vintage Copper Weathered Bronze White
Photoeye (Optional)	B C	120V 208V - 277V
Outlet Location (Optional)	B T	4" from Top of Base 12" from Top of Pole

Specifications

CONSTRUCTION:

Cast aluminum decorative anchor base. Cast aluminum removable access door. Grapevine post welded to base.

FINISH:

Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Hadco Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.

WARRANTY:

Three-year limited warranty.

Tenon/Top:

3" O.D.

Bolt Circle:

7" dia.

Decorative Anchor Base Post (302-) Specification Sheet

Project Name:	Location:	MFG: Hadco
Fixture Type:	Catalog No.:	Qty:

Anchor Rods:

(4) 1/2" dia. x 18" long zinc plated steel

Base Dimensions:

12 3/4" dia. x 22 3/4"

Shaft:

Grapevine Post

Wall Thickness:

.250"

Height:

9'

Pole EPA Values

Windspeed(mph)	Height
80	24.5300
110	13.8900
130	6.2000

