







220V 240V























	Configuration types	application	Size type	Lumen (lm)	Driver	А	В	C	kg
CR150B	RC	VPC/CPC/	W60L60	3500/5500	PSU/PSD -	595	595	86	6.0
	(Luminaire only)	PCV	W30L120			1195	295	102	6.5
	SM	Ceiling only	W60L60			630	630	-	9.5
	(Luminaire+bracket)		W30L120			1230	330	-	10.5












Min. 2 mm-


3b

## Option: Surface mounted(S.M)











© 2016 Philips Lighting Holding B.V.

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Philips Lighting Holding B.V. The Netherlands