



Complete fixture consists of Reflector Trim & Frame-in Kit. Select each separately

Frame-in Kit	Lamp	Voltage	Amps	Reflector Trim
1001FR18U	1-18W TTT (GX24q-2)	120/277V	0,17 / 0,08A	See Individual Reflector Trim Specification Sheets
1001FR18-347	1-18W TTT (GX24q-2)	347V	0,06A	
1001FR26U	1-26W TTT (GX24q-3)	120/277V	0,24 / 0,11A	
1001FR26-347	1-26W TTT (GX24q-3)	347V	0,09A	



**Features**

- Mounting Ring:** .032" (#22ga.) thick Galvanized Steel. Accommodates existing ceilings up to 2" thick. Attaches securely to any type of ceiling material without tools using (3) mounting straps provided. Includes adhesive backed aperture template.
- Trim Clips:** "Push In / Twist Out" clips hold reflector flush to ceiling.
- Junction Box:** 2" x 4" x 3-1/2" (22cu.in.) .032" (#22ga.) galvanized steel. cULus listed for maximum of 8 (#12ga.) through branch circuit conductors.
- Ballast:** 120V, 277V, 347V UL Listed Electronic Ballast, end of lamp life protection, class "P" thermally protected, class "A" sound rating. Minimum starting temperature is 0°F.
- Socket:** Four-pin base, molded thermoplastic socket, prewired with No. 18 AWM leads to ballast.
- Socket Housing:** .036" (#20ga.) Galvanized Steel housing attaches to reflector trim by spring clip for precise optic alignment.

**Markings**

cCSAus certified; suitable for damp locations.

Job Information	Type:
Job Name:	
Cat. No.:	
Lamp(s):	
Notes:	